

LED FLUSH MOUNTS

ETCHED WHITE GLASS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P2302-0930K9	Brushed Nickel	One-light	11" dia., 4" ht.	1 17w LED module included 1211 source lumens, 90CRI
P2302-2030K9	Antique Bronze			
P2303-0930K9	Brushed Nickel	One-light	13-1/4" dia., 4-3/4" ht.	1 17w LED module included 1211 source lumens, 90CRI
P2303-2030K9	Antique Bronze			

LED FEATURES

- 120V AC replaceable module
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with ELV type dimmers



P2302-0930K9



P2302-2030K9



P2303-0930K9



P2303-2030K9

LED FLUSH

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P350051-009-30	Brushed Nickel	One-light	11" dia., 4-3/16" ht.	1 17w LED module included 1452 source lumens, 90CRI
P350051-020-30	Antique Bronze			
P350052-009-30	Brushed Nickel	One-light	12-9/16" dia., 4-1/2" ht.	1 25w LED module included 2015 source lumens, 90CRI
P350052-020-30	Antique Bronze			
P350053-009-30	Brushed Nickel	One-light	11" dia., 4" ht.	1 17w LED module included 1452 source lumens, 90CRI
P350053-020-30	Antique Bronze			
P350054-009-30	Brushed Nickel	One-light	13-1/4" dia., 4-3/4" ht.	1 25w LED module included 2015 source lumens, 90CRI
P350054-020-30	Antique Bronze			

LED FEATURES

- 120V AC replaceable module
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with Triac or ELV dimmers
- JA-8 compliant



P350051-009-30



P350052-009-30



P350053-009-30



P350054-009-30



P350051-020-30



P350052-020-30



P350053-020-30



P350054-020-30