

GRESHAM

A display of substantial style, Gresham's frame was inspired by the elegance of traditional iron structures. Specific attention to forging details creates a distinctive collection for Transitional and Farmhouse interior spaces. Seeded glass shades and a Graphite finish pair together to complete the look.



P400164-143



P400164-143



P400165-143



P400166-143

FINISH

● Graphite - 143

SIX-LIGHT CHANDELIER

P400164-143 Graphite
28" dia., 22-1/2" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400165-143 Graphite
36" dia., 24-7/8" ht.
Overall ht. w/chain 99", wire 15'.
Nine candelabra base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400166-143 Graphite
Two-tier.
47-1/8" dia., 40-3/8" ht.
Overall ht. w/chain 163", wire 15'.
Five candelabra base lamps,
each 60w max.

GRESHAM

FINISH

- Graphite - 143

SEMI-FLUSH CONVERTIBLE

P350119-143 Graphite
Hanging and ceiling mount hardware included.
17-3/4" dia., 12" ht.
Overall ht. w/chain 50", wire 10'.
Three medium base lamps, each 60w max.

FOUR-LIGHT FOYER

P500164-143 Graphite
20" dia., 26-1/4" ht.
Overall ht. w/chain 100", wire 15'.
Four candelabra base lamps, each 60w max.

EIGHT-LIGHT FOYER

P500165-143 Graphite
24" dia., 41-3/8" ht.
Overall ht. w/chain 115-1/2", wire 15'.
Eight candelabra base lamps, each 60w max.

EIGHT-LIGHT CHANDELIER

P400180-143 Graphite
38" W., 17-1/2" ht., 13-7/8" d.
Overall ht. w/chain 91-1/2", wire 15'.
Eight candelabra base lamps, each 60w max.

ONE-LIGHT WALL BRACKET

P710055-143 Graphite
4-3/4" W., 15" ht.
Extends 5-3/4". H/CTR 10".
One candelabra base lamp, 60w max.



P350119-143
shown as semi-flush



P500164-143



P500165-143



P710055-143



P400180-143

P500165-143