

# Clarion

The versatile Clarion Collection features a simple etched opal glass or clear glass diffuser for a design that embraces minimalist modernity and functional task lighting.

## FINISHES

009 Brushed Nickel

012 Satin Brass

31M Matte Black

104 Polished Nickel



# Clarion

**P500429-009** Brushed Nickel  
9" dia., 11.37" ht.  
1 medium base, 60w max.



**P500430-009** Brushed Nickel  
10.5" dia., 15.87" ht.  
1 medium base, 60w max.



**P500429-012** Satin Brass  
9" dia., 11.37" ht.  
1 medium base, 60w max.



**P500430-012** Satin Brass  
10.5" dia., 15.87" ht.  
1 medium base, 60w max.



**P500429-31M** Matte Black  
9" dia., 11.37" ht.  
1 medium base, 60w max.



**P500430-31M** Matte Black  
10.5" dia., 15.87" ht.  
1 medium base, 60w max.



**P500429-104** Polished Nickel  
9" dia., 11.37" ht.  
1 medium base, 60w max.



**P500430-104** Polished Nickel  
10.5" dia., 15.87" ht.  
1 medium base, 60w max.





Featuring Clarion

# Clarion

**P500241-009** Brushed Nickel  
9" dia., 11.37" ht.  
1 medium base, 60w max.



**P500242-009** Brushed Nickel  
10.5" dia., 15.87" ht.  
1 medium base, 60w max.



**P500241-012** Satin Brass  
9" dia., 11.37" ht.  
1 medium base, 60w max.



**P500242-012** Satin Brass  
10.5" dia., 15.87" ht.  
1 medium base, 60w max.



**P500241-031** Matte Black  
9" dia., 11.37" ht.  
1 medium base, 60w max.



**P500242-031** Matte Black  
10.5" dia., 15.87" ht.  
1 medium base, 60w max.



**P500241-104** Polished Nickel  
9" dia., 11.37" ht.  
1 medium base, 60w max.



**P500242-104** Polished Nickel  
10.5" dia., 15.87" ht.  
1 medium base, 60w max.



# Clarion

Clarion embraces a minimalist simplicity, with a clear, tubular glass shade secured by a sleek cylindrical base for a precision look.

## FINISHES

- 009 Brushed Nickel
- 012 Satin Brass
- 015 Polished Chrome
- 031 Matte Black



P300299-009

- P300299-009** Brushed Nickel
  - P300299-012** Satin Brass
  - P300299-015** Polished Chrome
  - P300299-031** Matte Black
- 5" W., 12.62" ht., 4.25" D.  
1 medium base T10, 60w max.



# Clarion

- P300300-009** Brushed Nickel
  - P300300-012** Satin Brass
  - P300300-015** Polished Chrom
  - P300300-031** Matte Black
- 20.37" W., 5" ht.  
2 medium base T10, 60w max.



*shown vertical*

