



PCOWC SERIES Wall Pack

Full cutoff distribution with no uplight. Turtle friendly amber option available (AMB).

Product No.	Finish	Size	Source	Input
PCOWC-20LED-20	Bronze	8.22" W., 5.25" ht., 4.81" dia.	18w LED, 4000K, 1421 lumens	120 - 277V, 50 or 60 Hz   *Turtle Friendly ONLY PCOWC-45LED-20AMB
PCOWC-30LED-20		10.25" W., 5.6" ht., 6.25" dia.	29w LED, 4000K, 2246 lumens	
PCOWC-45LED-20			45w LED, 4000K, 3096 lumens	
PCOWC-45LED-20-AMB		32w LED, 590 NM		
PCOWC-20LED-28	White	8.22" W., 5.25" ht., 4.81" dia.	18w LED, 4000K, 1421 lumens	
PCOWC-30LED-28		10.25" W., 5.6" ht., 6.25" dia.	29w LED, 4000K, 2246 lumens	
PCOWC-45LED-28			45w LED, 4000K, 3096 lumens	
PCOWC-20LED-82	Metallic Gray	8.22" W., 5.25" ht., 4.81" dia.	18w LED, 4000K, 1421 lumens	
PCOWC-30LED-82		10.25" W., 5.6" ht., 6.25" dia.	29w LED, 4000K, 2246 lumens	
PCOWC-45LED-82			45w LED, 4000K, 3096 lumens	



PCOWC-20LED-20





PCOWC-45LED-20



PCOWC-30LED-20

Commercial Wall Pack

Product No.	Finish	Size	Source	Input
PCOWP-30LED-4K-BZ	Bronze	14-3/8" W., 9-1/4" ht., 7-3/8" D.	30w LED, 4000K, 80CRI, 351 lumens	120 - 277V, 50 or 60 Hz  
PCOWP-60LED-4K-BZ		8-9/16" W., 8-9/16" ht., 9-3/4" D.	60w LED, 4000K, 80CRI, 6700 lumens	
PCOWF-50LED-4K-BZ		14" W., 8-1/4" ht., 8-1/4" D.	50w LED, 4000K, 80CRI, 6350 lumens, full cutoff distribution with no uplight	



PCOWP-30LED-4K-BZ



PCOWF-50LED-4K-BZ



PCOWP-60LED-4K-BZ