



FEATURED PRODUCT

# Conte

Like a breath of fresh air, the organic design trend focuses on a connection with nature and a minimalist aesthetic. Incorporate plants and earthy tones like greens, blues, and warm neutrals to create a calming and serene atmosphere. The Conte LED ceiling fan's clean lines are inspired by the delicate elegance of a blooming flower with blades that gracefully curve upwards at the ends, evoking a sense of gentle movement even when the fan is still.

### STYLE YOUR ROOM

Find inspiration for your next project on [progresslighting.com](https://www.progresslighting.com)

## Conte

009 Brushed Nickel 028 Matte White 31M Matte Black

**P250105-009-30** Brushed Nickel  
52" dia., 14.06" ht.  
*Shown with Gray Weathered wood blades and light kit replaced by blank plate*

 Gray Weathered Wood



**P250105-028-30** Satin White  
52" dia., 14.06" ht.  
*Shown with Salt Aged Cypress blades*

 Salt Aged Cypress



**P250105-31M-30** Matte Black  
52" dia., 14.06" ht.  
*Shown with Matte Black blades*

 Matte Black



### ENERGY INFORMATION

**Airflow** 5037 cubic feet per minute  
**Electricity Use** 56.74 watts (excludes lights)  
**DOE Weighted CFM/W** 99 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light

### FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20)
- AC Motor
- Remote control with batteries included
- Add the P2667-31 WiFi remote control
- Reversible Motor
- Light Blank Plate included



### LAMPING

20w LED module, 3000K, 90CRI, 1865 source lumens, dimmable.

All fixtures:



Search the product number on [progresslighting.com](https://www.progresslighting.com) for full product details