

RATIO

A sleek metal frame supports a low-slung shade to create Ratio's casual modern style. The frame's proportion to the white linen drum shade evokes a perfect ratio for lighting. All fixtures include a polished glass diffuser that offers an elegant appeal.



P3604-09
shown as
pendant



P5015-09



P3604-20



P3604-09
shown as semi-flush



P5021-09



P5021-20

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

PAIR WITH

- Metric
- Finn
- Glaysé

SEMI-FLUSH CONVERTIBLE

P3604-09 Brushed Nickel
P3604-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 16" dia., 11-1/2" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 Three medium base lamps, each 75w max.

FOUR-LIGHT PENDANT

P5015-09 Brushed Nickel
P5015-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 24" dia., 15-7/8" ht.
 Overall ht. w/stem 82", wire 10'.
 Four medium base lamps, each 75w max.

SIX-LIGHT PENDANT

P5021-09 Brushed Nickel
P5021-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 30" dia., 19-1/8" ht.
 Overall ht. w/stem 85", wire 10'.
 Six medium base lamps, each 75w max.

P5015-20