

ELEVATE

Achieve a sleek and modern look with Elevate. Etched glass white shades paired with a Matte Black, Brushed Bronze or Polished Chrome frame provide an elegant contrast for Modern interior design settings.

ALSO AVAILABLE IN
Bath



P400022-031



P350040-031



P300020-031



P500151-031



P400021-031



P400022-031



P400023-031

FINISH

● Matte Black - 031

PAIR WITH

Penn
Ratio
Mod

THREE-LIGHT FLUSH MOUNT

P350040-031 Matte Black
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER

P400021-031 Matte Black
21-3/4" dia., 23" ht.
Overall ht. w/stem 89", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-031 Matte Black
27-3/8" dia., 23" ht.
Overall ht. w/stem 89", wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-031 Matte Black
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89", wire 15'.
Seven medium base lamps,
each 100w max.

MINI-PENDANT

P500151-031 Matte Black
3-7/8" dia., 7" ht.
Overall ht. w/stem 73", wire 10'.
One medium base lamp,
100w max.

ELEVATE

FINISH

- Polished Chrome - 015

ONE-LIGHT WALL BRACKET

P300020-015 Polished Chrome
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT SEMI-FLUSH

P350040-015 Polished Chrome
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

ONE-LIGHT FLUSH MOUNT

P350105-015-30 Polished Chrome
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 source lumens.



THREE-LIGHT CHANDELIER

P400021-015 Polished Chrome
21-3/4" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-015 Polished Chrome
27-3/8" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-015 Polished Chrome
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89"; wire 15'.
Seven medium base lamps,
each 100w max.

MINI-PENDANT

P500151-015 Polished Chrome
3-7/8" dia., 7" ht.
Overall ht. w/stem 73", wire 10'.
One medium base lamp,
100w max.



P350040-015



P350105-015-30



P300020-015



P500151-015



P400021-015



P400022-015



P400023-015

P400022-015

ELEVATE

FINISH

● Brushed Bronze - 109

ONE-LIGHT WALL BRACKET

P300020-109 Brushed Bronze
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT SEMI-FLUSH

P350040-109 Brushed Bronze
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

ONE-LIGHT FLUSH MOUNT

P350105-109-30 Brushed Bronze
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 source lumens.



THREE-LIGHT CHANDELIER

P400021-109 Brushed Bronze
21-3/4" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-109 Brushed Bronze
27-3/8" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-109 Brushed Bronze
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89"; wire 15'.
Seven medium base lamps,
each 100w max.

MINI-PENDANT

P500151-109 Brushed Bronze
3-7/8" dia., 7" ht.
Overall ht. w/stem 73", wire 10'.
One medium base lamp,
100w max.



P350040-109



P350105-109-30



P300020-109



P500151-109



P400021-109



P400022-109



P400023-109

P400022-109

PROGRESSLIGHTING.COM

ELEVATE

Achieve a mid-century modern look with Elevate, which boasts glass shades and a frame inspired by modern styling. Brushed Bronze and Polished Chrome finish options also available.

ALSO AVAILABLE IN
Collections



P300021-031



P300021-031



P300020-031



P300022-031



P300023-031

FINISH

● Matte Black - 031

ONE-LIGHT BATH

P300020-031 Matte Black
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300021-031 Matte Black
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300022-031 Matte Black
24-3/4" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300023-031 Matte Black
34-1/2" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

ELEVATE

FINISH

● Brushed Bronze - 109

ONE-LIGHT BATH

P300020-109 Brushed Bronze
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.



P300020-109



P300021-109

TWO-LIGHT BATH

P300021-109 Brushed Bronze
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.



P300022-109

THREE-LIGHT BATH

P300022-109 Brushed Bronze
24-3/4" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.



P300023-109

FOUR-LIGHT BATH

P300023-109 Brushed Bronze
34-1/2" W., 7-1/2" ht.
Extends 7-3/4". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

ELEVATE

FINISH

● Polished Chrome - 015

ONE-LIGHT BATH

P300020-015 Polished Chrome
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.



P300021-015



P300020-015

TWO-LIGHT BATH

P300021-015 Polished Chrome
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.



P300022-015

THREE-LIGHT BATH

P300022-015 Polished Chrome
24-3/4" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.



P300023-015

FOUR-LIGHT BATH

P300023-015 Polished Chrome
34-1/2" W., 7-1/2" ht.
Extends 7-3/4". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.