

HANGAR

Fixtures in the Hangar collection are fun, light and airy pieces – perfect for both casual and modern homes. A sophisticated, statement-making frame occupies a large visual space. Modern wire basket forms are finished in Brushed Nickel with graphite accents or Antique Bronze and natural brass accents to complete the design.



P500117-009



P500115-009



P400105-009



P400106-009



P710043-009



P350102-009



P500116-009

FINISH

- Brushed Nickel - 009

PAIR WITH

Astra
Zag

SEMI-FLUSH CONVERTIBLE

P350102-009 Brushed Nickel Hanging and ceiling mount hardware included. Vintage Linen Shade. 16" dia., 13-1/4" ht. Overall ht. w/stem 78-1/2", wire 10'. Two medium base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400105-009 Brushed Nickel 30" dia., 19-3/4" ht.* Overall ht. w/stem 77", wire 15'. Five medium base lamps, each 60w max.

EIGHT-LIGHT CHANDELIER

P400106-009 Brushed Nickel 40" dia., 24-7/8" ht.* Overall ht. w/stem 91-1/2", wire 15'. Eight medium base lamps, each 60w max.

MINI-PENDANT

P500115-009 Brushed Nickel 13" dia., 9-5/8" ht. Overall ht. w/stem 76-1/2", wire 10'. One medium base lamp, 60w max.

ONE-LIGHT PENDANT

P500116-009 Brushed Nickel Vintage Linen Shade. 20" dia., 26" ht. Overall ht. w/stem 92", wire 15'. One medium base lamp, 100w max.

THREE-LIGHT PENDANT

P500117-009 Brushed Nickel Vintage Linen Shade. 24" dia., 24-1/4" ht. Overall ht. w/stem 90", wire 15'. Three medium base lamps, each 75w max.

WALL BRACKET

P710043-009 Brushed Nickel 5" W., 8-3/4" ht.* Extends 4-1/2". H/CTR 4". One medium base lamp, 60w max.

*Fixture dimension does not include lamps.

All fixtures shown with P7825-01 or P7827-01 lamps, not included.

HANGAR

FINISH

- Antique Bronze - 020

SEMI-FLUSH CONVERTIBLE

P350102-020 Brushed Nickel
Hanging and ceiling mount hardware included. Vintage Linen Shade. 16" dia., 13-1/4" ht.
Overall ht. w/stem 78-1/2", wire 10'.
Two medium base lamps, each 60w max.



P710043-020

FIVE-LIGHT CHANDELIER

P400105-020 Antique Bronze
30" dia., 19-3/4" ht.*
Overall ht. w/stem 77", wire 15'.
Five medium base lamps, each 60w max.



P400105-020

EIGHT-LIGHT CHANDELIER

P400106-020 Antique Bronze
40" dia., 24-7/8" ht.*
Overall ht. w/stem 91-1/2", wire 15'.
Eight medium base lamps, each 60w max.



P400106-020

MINI-PENDANT

P500115-020 Antique Bronze
13" dia., 9-5/8" ht.
Overall ht. w/stem 76-1/2", wire 10'.
One medium base lamp, 60w max.



P350102-020

ONE-LIGHT PENDANT

P500116-020 Antique Bronze
Vintage Linen Shade.
20" dia., 26" ht.
Overall ht. w/stem 92", wire 15'.
One medium base lamp, 100w max.



P500116-020

THREE-LIGHT PENDANT

P500117-020 Antique Bronze
Vintage Linen Shade.
24" dia., 24-1/4" ht.
Overall ht. w/stem 90", wire 15'.
Three medium base lamps, each 75w max.



P500117-020

WALL BRACKET

P710043-020 Antique Bronze
5" W., 8-3/4" ht.*
Extends 4-1/2". H/CTR 4".
One medium base lamp, 60w max.

*Fixture dimension does not include lamps.

All fixtures shown with P7825-01 or P7827-01 lamps, not included.