

# UNION SQUARE

Originally inspired by historical reproduction gas lanterns, Union Square now offers a four-light chandelier and five-light linear island fixture. The simple geometric form features a Stainless Steel frame that is paired with vintage-style light bulbs. Mechanical details such as exaggerated knobs provide character to the form.



ALSO AVAILABLE IN

- Bath
- Outdoor



P400112-135



P400145-135

**FINISH**  
● Stainless Steel - 135

**PAIR WITH**  
Remix  
Turnbury

**FOUR-LIGHT CHANDELIER**  
**P400112-135** Stainless Steel  
20" W., 9-3/4" ht.  
Overall ht. w/stems 76-1/2", wire 15'.  
Four medium base lamps,  
each 60w max.

**FIVE-LIGHT ISLAND**  
**P400145-135** Stainless Steel  
38" W., 9-3/4" ht., 8-1/2" d.  
Overall ht. w/stems 76", wire 15'.  
Five medium base lamps,  
each 60w max.

**ONE-LIGHT BRACKET**  
**P710038-135** Stainless Steel  
5-1/4" W., 12" ht.  
Extends 5". H/CTR 6".  
One medium base lamp,  
60w max.

All fixtures shown with  
P7825-01 lamps, not included.



P710038-135  
shown with P7825-01  
vintage lamp



P710038-135  
shown with P7827-01  
vintage lamp

P400112-135

# UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open bottom on wall lanterns provides easy access for cleaning and relamping.



*ALSO AVAILABLE IN*

Collections  
Bath



P560005-135



P560004-135



P560005-135



P560006-135



P550018-135



P550007-135

*FINISH*  
● Stainless Steel - 135

*FLUSH MOUNT*  
**P550007-135** Stainless Steel  
12-3/8" sq., 5-1/2" ht.  
Two medium base lamps,  
each 60w max.

*SMALL WALL-LANTERN*  
**P560004-135** Stainless Steel  
6-1/2" W., 15-7/8" ht.  
Extends 5-1/2". H/CTR 6-1/4".  
One medium base lamp,  
100w max.

*MEDIUM WALL-LANTERN*  
**P560005-135** Stainless Steel  
7-7/8" W., 19-3/8" ht.  
Extends 6-1/2". H/CTR 7-3/4".  
One medium base lamp,  
100w max.

*LARGE WALL-LANTERN*  
**P560006-135** Stainless Steel  
9-3/4" W., 23-5/8" ht.  
Extends 8". H/CTR 9-5/8".  
One medium base lamp,  
100w max.

*HANGING LANTERN*  
**P550018-135** Stainless Steel  
7" sq., 27-3/8" ht.  
Overall ht. w/chain 102-1/2", wire 10'.  
One medium base lamp,  
100w max.

*All fixtures shown with P7827-01  
vintage lamps, not included.*

# UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open top and bottom on fixture provides easy access for cleaning and relamping.



## ALSO AVAILABLE IN

Collections  
Outdoor



P300135-135



P710038-135  
shown with P7825-01  
vintage lamp



P710038-135  
shown with P7827-01  
vintage lamp

## FINISH

● Stainless Steel - 135

## ONE-LIGHT BATH

**P710038-135** Stainless Steel  
5-1/4" sq., 12" ht.  
Extends 5". H/CTR 6".  
One medium base lamp,  
60w max.

## TWO-LIGHT BATH

**P300135-135** Stainless Steel  
16" W., 4-1/2" ht.  
Extends 5". H/CTR 2-1/4".  
Two medium base lamps,  
each 60w max.

## FOUR-LIGHT BATH

**P300136-135** Stainless Steel  
30" W., 4-1/2" ht.  
Extends 5". H/CTR 2-1/4".  
Four medium base lamps,  
each 60w max.



P300135-135  
shown with P7825-01  
vintage lamps



P300136-135  
shown with P7827-01  
vintage lamps