

DEBUT

Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.



ALSO AVAILABLE IN

Bath



P400015-009



P350036-009



P400015-009
shown with
P860003-001 shade



P400017-009
shown with
P860002-001 shade



P300008-009

P300008-009
shown with
P860002-001 shade



P860002-001

P860003-001



P400016-009

FINISH

● Brushed Nickel -009

PAIR WITH

Remix
Staunton

WALL BRACKET

P300008-009 Brushed Nickel
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-009 Brushed Nickel
28" dia., 27-1/2" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-009 Brushed Nickel
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-009 Brushed Nickel
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

All fixtures shown with P7825-01
vintage lamps, not included.

DEBUT

FINISH

● Graphite - 143

WALL BRACKET

P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-143 Graphite
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-143 Graphite
28" dia., 27-1/2" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-143 Graphite
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-143 Graphite
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

*All fixtures shown with P7825-01
vintage lamps, not included.*



P350036-143
shown with
P860002-001 shade



P400015-143



P400017-143
shown with
P860003-001 shade



P300008-143



P300008-143

shown with
P860003-001 shade

P400016-143



P860002-001



P860003-001

P400015-143

DEBUT

Delicate details and warm finish options, including Graphite and Brushed Nickel, create statement making focal pieces for a variety of interiors. Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.

ALSO AVAILABLE IN
Collections



P300009-143
Shown with
P860003-001 shade

PROGRESSLIGHTING.COM



P300009-143
shown with
P860003-001 shade



P300008-143



P300010-143
shown with
P860003-001 shade



P300011-143
shown with
P860002-001 shade



P300009-009
shown with
P860002-001 shade



P300008-009
shown with
P860003-001 shade



P300010-009
shown with
P860003-001 shade



P300011-009

FINISHES

- Brushed Nickel - 009
- Graphite - 143

ONE-LIGHT BATH

P300008-009 Brushed Nickel
P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300009-009 Brushed Nickel
P300009-143 Graphite
14-1/4" W., 7-7/8" ht.
Extends 5-3/4". H/CTR 5-5/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300010-009 Brushed Nickel
P300010-143 Graphite
23-3/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300011-009 Brushed Nickel
P300011-143 Graphite
30-1/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Four medium base lamps,
each 60w max.

P860002-001
Etched glass shade.

P860003-001
Seeded glass shade.

All fixtures shown with P7825-01
vintage lamps, not included.

All fixtures mount up or down.



P860002-001



P860003-001