

# FONTAYNE

With updated designs that honor the charm of early American styling, Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces. Impressive graphic elements take center stage, while candelabra lights highlight subtle curves. Dual tone finish combinations include Antique Bronze with faux oak accents or Brushed Nickel with weathered gray accents.



P400080-020

PROGRESSLIGHTING.COM



P400080-020



P500088-020

## FINISH

● Antique Bronze - 020

## PAIR WITH

Galley  
Conestee  
Hansford

## FOUR-LIGHT CHANDELIER

**P400080-020** Antique Bronze  
15-3/4" dia., 30" ht.  
Overall ht. w/stem 105", wire 15'.  
Four candelabra base lamps,  
each 60w max.

## SIX-LIGHT CHANDELIER

**P400081-020** Antique Bronze  
22" dia., 24-3/4" ht.  
Overall ht. w/stem 111-1/2", wire 15'.  
Six candelabra base lamps,  
each 60w max.

## SIX-LIGHT LINEAR CHANDELIER

**P400082-020** Antique Bronze  
36" W., 22" d., 15-3/4" ht.  
Overall ht. w/stems 103-1/2", wire 15'.  
Six candelabra base lamps,  
each 60w max.

## TWELVE-LIGHT CHANDELIER

**P400083-020** Antique Bronze  
32" dia., 28-3/4" ht.  
Overall ht. w/stem 107", wire 15'.  
Twelve candelabra base lamps,  
each 60w max.

## FOUR-LIGHT PENDANT

**P500088-020** Antique Bronze  
14" Sq., 25" ht.  
Overall ht. w/chain 99", wire 15'.  
Four candelabra base lamps,  
each 60w max.

## SIX-LIGHT PENDANT

**P500089-020** Antique Bronze  
20" Sq., 32" ht.  
Overall ht. w/chain 107-1/2", wire 15'.  
Six candelabra base lamps,  
each 60w max.

*All fixtures shown with P7826-01 vintage lamps, not included.*



P400081-020



P500089-020



P400083-020



P400082-020

# FONTAYNE

## FINISH

● Brushed Nickel - 009

### FOUR-LIGHT CHANDELIER

**P400080-009** Brushed Nickel  
15-3/4" dia., 30" ht.  
Overall ht. w/stem 105", wire 15'.  
Four candelabra base lamps,  
each 60w max.

### SIX-LIGHT CHANDELIER

**P400081-009** Brushed Nickel  
22" dia., 24-3/4" ht.  
Overall ht. w/stem 111-1/2", wire 15'.  
Six candelabra base lamps,  
each 60w max.

### SIX-LIGHT LINEAR CHANDELIER

**P400082-009** Brushed Nickel  
36" W., 22" d., 15-3/4" ht.  
Overall ht. w/stems 103-1/2", wire 15'.  
Six candelabra base lamps,  
each 60w max.

### TWELVE-LIGHT CHANDELIER

**P400083-009** Brushed Nickel  
32" dia., 28-3/4" ht.  
Overall ht. w/stem 107", wire 15'.  
Twelve candelabra base lamps,  
each 60w max.

### FOUR-LIGHT PENDANT

**P500088-009** Brushed Nickel  
14" Sq., 25" ht.  
Overall ht. w/chain 99", wire 15'.  
Four candelabra base lamps,  
each 60w max.

### SIX-LIGHT PENDANT

**P500089-009** Brushed Nickel  
20" Sq., 32" ht.  
Overall ht. w/chain 107-1/2", wire 15'.  
Six candelabra base lamps,  
each 60w max.

*All fixtures shown with P7826-01 vintage lamps, not included.*



P400080-009



P500088-009



P400081-009



P500089-009



P400083-009



P400082-009

P400080-009

PROGRESSLIGHTING.COM