

NOMA

Mixed finishes, such as Polished Nickel with silver ridge accents and Antique Bronze with champagne accents are highlighted in Noma. Soft angles and curving lines created from flat metal straps elegantly frame etched white glass shades.



P400012-020



P350034-020



P400011-020



P400014-020



P400013-020



P500007-020



P350035-020

P710005-020

FINISH

● Antique Bronze - 020

PAIR WITH

Ratio
Evoke

SEMI-FLUSH CONVERTIBLE

P350034-020 Antique Bronze Hanging and ceiling mount hardware included. 15-5/8" dia., 12-1/2" ht. Overall ht. w/chain 51-1/2"; wire 10'. Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400011-020 Antique Bronze 23" dia., 17-7/8" ht. Overall ht. w/chain 92-1/2"; wire 15'. Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400012-020 Antique Bronze 28-1/2" dia., 26" ht. Overall ht. w/chain 101"; wire 15'. Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400013-020 Antique Bronze Two-tier. 34" dia., 32" ht. Overall ht. w/chain 155"; wire 15'. Nine medium base lamps, each 100w max.

FOUR-LIGHT FOYER PENDANT

P400014-020 Antique Bronze 16" dia., 29-1/4" ht. Overall ht. w/chain 104"; wire 15'. Four candelabra base lamps, each 60w max.

MINI-PENDANT

P500007-020 Antique Bronze 7-3/8" dia., 6-1/2" ht. Overall ht. w/stem 72-1/2"; wire 10'. One medium base lamp, 100w max.

WALL BRACKET

P710005-020 Antique Bronze 7-3/8" W., 18-5/8" ht. Extends 8-3/8". H/CTR 6-3/4". One medium base lamp, 100w max.

TWO-LIGHT FLUSH MOUNT

P350035-020 Antique Bronze 14-7/8" dia., 7-3/4" ht. Two medium base lamps, each 60w max.

NOMA

FINISH

● Polished Nickel - 104

SEMI-FLUSH CONVERTIBLE

P350034-104 Polished Nickel
Hanging and ceiling mount hardware included.
15-5/8" dia., 12-1/2" ht.
Overall ht. w/chain 51-1/2"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400011-104 Polished Nickel
23" dia., 17-7/8" ht.
Overall ht. w/chain 92-1/2"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400012-104 Polished Nickel
28-1/2" dia., 26" ht.
Overall ht. w/chain 101"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400013-104 Polished Nickel
Two-tier.
34" dia., 32" ht.
Overall ht. w/chain 155"; wire 15'.
Nine medium base lamps, each 100w max.

FOUR-LIGHT FOYER PENDANT

P400014-104 Polished Nickel
16" dia., 29-1/4" ht.
Overall ht. w/chain 104"; wire 15'.
Four candelabra base lamps, each 60w max.

MINI-PENDANT

P500007-104 Polished Nickel
7-3/8" dia., 6-1/2" ht.
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp, 100w max.

WALL BRACKET

P710005-104 Polished Nickel
7-3/8" W., 18-5/8" ht.
Extends 8-3/8". H/CTR 6-3/4".
One medium base lamp, 100w max.

TWO-LIGHT FLUSH MOUNT

P350035-104 Polished Nickel
14-7/8" dia., 7-3/4" ht.
Two medium base lamps, each 60w max.



P400012-104



P350034-104



P400011-104



P400014-104



P400013-104



P500007-104



P350035-104

P710005-104