

BONITA NEW

Inspired at its roots by an understated beauty and a breathtaking formal elegance, the Bonita collection makes a stunning addition to any luxurious living space. This gaze-grabbing modern collection grants a slight nod to antique candle-like fixtures with graceful, arrow drum shades held in place by light bases supported by elegantly curved arms. Bonita's signature elegant design is ideal for illuminating family meals at your dining table or around a kitchen island.



P400227-012



P400227-012



P400227-031



P500285-012



P500285-031



P710018-012



P710019-012



P710018-031



P710019-031

FINISHES

- Satin Brass - 012
- Matte Black - 031

PAIR WITH

Celeste
Carriage Hill

SIX-LIGHT CHANDELIER

P400227-012 Satin Brass
P400227-031 Matte Black
30-1/2" dia., 24" ht.
Overall ht. w/stem 90", wire 15'.
Six candelabra base lamps,
each 40w max.

FOUR-LIGHT FOYER

P500285-012 Satin Brass
P500285-031 Matte Black
23" dia., 25-7/8" ht.
Overall ht. w/stem 92", wire 15'.
Four candelabra base lamps,
each 40w max.

WALL BRACKET

P710018-012 Satin Brass
P710018-031 Matte Black
4-1/2" W., 17-1/8" ht.
Extends 6-7/8". H/CTR 13-5/8".
One candelabra base lamp,
40w max.

WALL BRACKET

P710019-012 Satin Brass
P710019-031 Matte Black
13-5/8" W., 17-1/4" ht.
Extends 6-7/8". H/CTR 13-5/8".
Two candelabra base lamps,
each 40w max.

BONITA



P400227-015 **N**



P400227-009 **N**



P500285-015 **N**



P500285-009 **N**



P710018-015

P710019-015



P710018-009

P710019-009



P710018-020

P710019-020

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 20

SIX-LIGHT CHANDELIER

P400227-009 Brushed Nickel
P400227-015 Polished Chrome
 30-1/2" dia., 24" ht.
 Overall ht. w/stem 90", wire 15'.
 Six candelabra base lamps,
 each 40w max.

FOUR-LIGHT FOYER

P500285-009 Brushed Nickel
P500285-015 Polished Chrome
 23" dia., 25-7/8" ht.
 Overall ht. w/stem 92", wire 15'.
 Four candelabra base lamps,
 each 40w max.

WALL SCONCE

P710018-009 Brushed Nickel
P710018-015 Polished Chrome
P710018-020 Antique Bronze
 4-1/2" W., 17-1/8" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 One candelabra base lamp,
 40w max.

WALL SCONCE

P710019-009 Brushed Nickel
P710019-015 Polished Chrome
P710019-020 Antique Bronze
 13-5/8" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 Two candelabra base lamps,
 each 40w max.

P400227-015

BONITA

Bonita sconces have a traditional elegance to complement luxurious living with an understated beauty. Crisp metal fittings support a graceful frame and candle topped with a linen shade. Coordinate with Marché or Glimmer collections to add a variation of textures.



ALSO AVAILABLE IN
Collections



P710019-009



P710018-009



P710019-009



P710018-012 *N*



P710019-012 *N*



P710018-015



P710019-015



P710018-020



P710019-020



P710018-031 *N*



P710019-031 *N*

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Polished Chrome - 015
- Antique Bronze - 020
- Matte Black - 031

WALL BRACKET

P710018-009 Brushed Nickel
P710018-012 Satin Brass
P710018-015 Polished Chrome
P710018-020 Antique Bronze
P710018-031 Matte Black
 9" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 One candelabra base lamp,
 40w max.

WALL BRACKET

P710019-009 Brushed Nickel
P710019-012 Satin Brass
P710019-015 Polished Chrome
P710019-020 Antique Bronze
P710019-031 Matte Black
 13-5/8" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 Two candelabra base lamps,
 each 40w max.