

VOLO LED

Volo fixtures feature a modern repeating circular frame. Etched opal glass shades are seamlessly secured to provide a clean, contemporary look to your home. The modern LED source delivers crisp, high quality light that is the perfect choice for both general and task lighting.



P300063-009-30



P300063-009-30



P300064-009-30



P300065-009-30

FINISH

● Brushed Nickel - 009

ONE-LIGHT BATH

P300063-009-30 Brushed Nickel
10" W., 5-1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
One 9w LED module, 3000K,
90 CRI, 624 source lumens.

TWO-LIGHT BATH

P300064-009-30 Brushed Nickel
16" W., 5 1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
Two 9w LED modules, 3000K,
90 CRI, 624 source lumens per module.

THREE-LIGHT BATH

P300065-009-30 Brushed Nickel
24" W., 5-1/2" ht.
Extends 4-5/8". H/CTR 2-3/4".
Three 9w LED modules, 3000K,
90 CRI, 624 source lumens per module.

All fixtures can be installed vertically or horizontally.

All fixtures:

