

CREIGHTON

Creighton features clear water glass with Antique Bronze or Textured Black finish options. The frame's linear details are riveted to enhance mechanical detailing of the fixture. Wall, post and hanging lantern options available.



P560031-031



P560031-020



P560032-031



P560032-020



P560033-031



P560033-020



P540009-031



P540009-020



P550009-020



P550009-031

FINISHES

- Antique Bronze - 020
- Textured Black - 031

POST LANTERN

P540009-020 Antique Bronze
P540009-031 Textured Black
 10-1/2" dia., 21-3/4" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P550009-020 Antique Bronze
P550009-031 Textured Black
 10-1/2" dia., 21-5/8" ht.
 Overall ht. w/chain 96-1/2"; wire 10'.
 One medium base lamp,
 100w max.

SMALL WALL-LANTERN

P560031-020 Antique Bronze
P560031-031 Textured Black
 6" W., 11-1/2" ht.
 Extends 7-1/4". H/CTR 2-3/8".
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560032-020 Antique Bronze
P560032-031 Textured Black
 8-3/8" W., 15-3/4" ht.
 Extends 9-3/8". H/CTR 3".
 One medium base lamp,
 100w max.

LARGE WALL-LANTERN

P560033-020 Antique Bronze
P560033-031 Textured Black
 10-1/2" W., 19-1/4" ht.
 Extends 11-1/8". H/CTR 3".
 One medium base lamp,
 100w max.

P550009-020