

CADENCE

The Cadence collection showcases classic lantern styling. Clear water glass panels surround traditional lighting clusters. A curved, Mediterranean-influenced frame is finished in Textured Black and Oil rubbed Bronze.



P6542-108



P6080-108



P6542-108



P6639-108



P6638-108



P6640-108



P6442-108

FINISH

- Oil Rubbed Bronze - 108

SMALL WALL-LANTERN

P6080-108 Oil Rubbed Bronze
6" W., 16-1/4" ht.
Extends 7-1/4". H/CTR 7-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P6638-108 Oil Rubbed Bronze
8" W., 21-1/4" ht.
Extends 9-3/8". H/CTR 9-7/8".
Two candelabra base lamps,
each 60w max.

POST LANTERN

P6442-108 Oil Rubbed Bronze
10" sq., 22-5/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P6542-108 Oil Rubbed Bronze
10" sq., 24" ht.
Overall ht. w/chain 99-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P6639-108 Oil Rubbed Bronze
10" W., 26-5/8" ht.
Extends 11-1/2". H/CTR 9-5/8".
Three candelabra base lamps,
each 60w max.

EXTRA-LARGE WALL LANTERN

P6640-108 Oil Rubbed Bronze
12-1/4" W., 32" ht.
Extends 13-3/4". H/CTR 11-5/8".
Four candelabra base lamps,
each 60w max.

CADENCE

FINISH

- Textured Black - 31

SMALL WALL LANTERN

P6626-31CD Textured Black
6-1/8" W., 18-7/8" ht.
Extends 7-1/2". H/CTR 9-1/4".
One candelabra base lamp,
60w max.

MEDIUM WALL LANTERN

P6627-31MD Textured Black
8" W., 24-3/4" ht.
Extends 9-1/4". H/CTR 13-3/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P6628-31MD Textured Black
10" W., 31" ht.
Extends 11-3/8". H/CTR 14-1/8".
One medium base lamp,
100w max.

EXTRA LARGE WALL LANTERN

P6629-31MD Textured Black
12" W., 38" ht.
Extends 13-1/4". H/CTR 18-1/4".
One medium base lamp,
100w max.



N

P6626-31CD



N

P6627-31MD



N

P6629-31MD



N

P6628-31MD



P6627-31MD

PROGRESSLIGHTING.COM

N New Product