

# Dallam

009 Brushed Nickel 31M Matte Black



The Dallam ceiling fan gracefully creates the impression of a flower in bloom as its six blades wrap around gently around its opal white shade. This 60-inch design is available in Silver and Chestnut with a Brushed Nickel housing or Matte Black and Rustic Charcoal with a Matte Black housing, offering a rustic presence to any space it occupies. The white opal shaded light kit is an integrated 20W LED module offering color-selectable 90 CRI illumination in a gentle 2700K, 3000K soft light or a bright 5000K light that you select from the included full-function remote control. Its DC motor is whisper-quiet, and UL damp location listed for indoor and outdoor covered areas.



P250103-31M-CS



# Dallam

**P250103-009-CS** Brushed Nickel  
60" dia., 14" ht.  
*Shown with Silver blades*




-  Silver
-  Dark Cherry



**P250103-31M-CS** Matte Black  
60" dia., 14" ht.  
*Shown with Matte Black blades*

-  Walnut
-  Matte Black



<b>3-CCT</b> SELECTABLE	 2700K
	 3000K
	 5000K

### ENERGY INFORMATION

**Airflow** 5787 cubic feet per minute  
**Electricity Use** 33 watts (excludes lights)  
**DOE Weighted CFM/W** 201 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

### FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included

### LAMPING

20w LED Module, 2700K, 3000K, 5000K, 90 CRI, 1700 source lumens, dimmable.

All fixtures:

