

Elara

Elara features a slender, chic form with a stylized finial inspired by a chess pawn for a classically modern style.

FINISHES

009 Brushed Nickel

31M Matte Black

163 Vintage Brass



P400293-163

Elara

P400294-163 Vintage Brass
30" dia., 10.37" ht.
6 candelabra base, 60w max.



P500363-163 Vintage Brass
15" dia., 31.37" ht.
4 candelabra base, 60w max.



P400293-163 Vintage Brass
22.87" dia., 10.37" ht.
4 candelabra base, 60w max.
shown with P860060-000 shade



P710107-163 Vintage Brass
10.37" W., 16.62" ht., 4.37" D.
2 candelabra base, 60w max.



P710106-163 Vintage Brass
5.75" W., 16.62" ht., 4.37" D.
1 candelabra base, 60w max.
shown with P860060-000 shade



ALSO IN



Bath

ACCESSORY SHADES See p. 342 for details



P860059-000
Drum
White Linen



P860060-000
Tapered
White Linen



P860061-068
Clear Glass



P860061-029
Etched White Glass

Search the product number on progresslighting.com for full product details



FEATURED PRODUCT

Elara

Rich, luxurious blue and gold furniture and décor pop against a crisp white color palette. The versatile Elara Collection's slender, chic form has stylized finials inspired by a chess pawn. The lighting has a simple, elegant style when used without a shade, or easily change the fixture's look by selecting a clear glass shade for modern flair and linen or opal shades for a more traditional design (Shades sold separately).

STYLE YOUR ROOM

Find inspiration for your next project on [progresslighting.com](https://www.progresslighting.com)

Elara

P400294-31M Matte Black
30" dia., 10.37" ht.
6 candelabra base, 60w max.
shown with P860061-068 shade



P500363-31M Matte Black
15" dia., 31.37" ht.
4 candelabra base, 60w max.



P400293-31M Matte Black
22.87" dia., 10.37" ht.
4 candelabra base, 60w max.



P710107-31M Matte Black
10.37" W., 16.62" ht., 4.37" D.
2 candelabra base, 60w max.
shown with P860061-068 shade



P710106-31M Matte Black
5.75" W., 16.62" ht., 4.37" D.
1 candelabra base, 60w max.



ALSO IN



Bath

ACCESSORY SHADES See p. 342 for details



P860059-000
Drum
White Linen



P860060-000
Tapered
White Linen



P860061-068
Clear Glass



P860061-029
Etched White Glass

Search the product number on [progresslighting.com](https://www.progresslighting.com) for full product details

Elara

Elara features a slender, chic form with a stylized finial inspired by a chess pawn for a classically modern style.

FINISHES

009 Brushed Nickel

31M Matte Black

163 Vintage Brass



P400293-009

Elara

P400294-009 Brushed Nickel
30" dia., 10.37" ht.
6 candelabra base, 60w max.
shown with P860059-000 shade



P500363-009 Brushed Nickel
15" dia., 31.37" ht.
4 candelabra base, 60w max.



P400293-009 Brushed Nickel
22.87" dia., 10.37" ht.
4 candelabra base, 60w max.



P710107-009 Brushed Nickel
10.37" W., 16.62" ht., 4.37" D.
2 candelabra base, 60w max.
shown with P860059-000 shade



P710106-009 Brushed Nickel
5.75" W., 16.62" ht., 4.37" D.
1 candelabra base, 60w max.



ALSO IN



Bath

ACCESSORY SHADES See p. 342 for details



P860059-000
Drum
White Linen



P860060-000
Tapered
White Linen



P860061-068
Clear Glass



P860061-029
Etched White Glass

Search the product number on progresslighting.com for full product details

Elara

Elara features a slender, chic form with a stylized finial inspired by a chess pawn for a classically modern style.

FINISHES

- 009 Brushed Nickel
- 31M Matte Black
- 163 Vintage Brass



P300357-009

- P300359-009** Brushed Nickel
- P300359-31M** Matte Black
- P300359-163** Vintage Brass
- 31.65" W., 11.5" ht.
- 4 candelabra base, 60w max.



Search the product number on progresslighting.com for full product details

Elara

- P300358-009** Brushed Nickel
- P300358-31M** Matte Black
- P300358-163** Vintage Brass
- 22.12" W., 11.5" ht.
- 3 candelabra base, 60w max.



- P300357-009** Brushed Nickel
- P300357-31M** Matte Black
- P300357-163** Vintage Brass
- 12.5" W., 11.5" ht.
- 2 candelabra base, 60w max.



- P300356-009** Brushed Nickel
- P300356-31M** Matte Black
- P300356-163** Vintage Brass
- 4.75" W., 11.5" ht., 5" D.
- 1 candelabra base, 60w max.



Search the product number on progresslighting.com for full product details