

Fairway LED Surface Mount

The Fairway 7 in. Surface Mount LED Light combines sleek design with value-driven functionality. Its durable metal trim is coated in a clean white finish paired with a glare-free polycarbonate lens. A 1000-lumen light engine delivers a total of 850 lumens of 3000K, 90 CRI illumination that is dimmable using TRIAC dimmers and is CA Title 24 Compliant. Its classic design has a gasketed, UL wet location listed construction and is quickly and easily installed by mounting directly into a j-box in a variety of residential and commercial settings.

P810042-028-30 Satin White
7" dia., 1.10" ht.
11w Integrated LED, 3000K,
90 CRI, 857 delivered lumens.



Installation Sequence

