

Fanin

015 Polished Chrome

31M Matte Black

P250114-015-30 Polished Chrome
20.75" dia., 10" ht.



P250114-31M-30 Matte Black
20.75" dia., 10" ht.



ENERGY INFORMATION*

Airflow N/A
Electricity Use N/A
DOE Weighted CFM/W N/A

*Data not available at time of printing



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- 360° Oscillation
- Limited Lifetime Warranty
- Close to Ceiling Mount
- DC Motor
- Damp Rated
- Remote Control with Batteries Included
- Edge lit LEDs
- Rust Proof Blades

LAMPING

31W LED Strip, 3000K, 90 CRI,
1700 Source lumens, dimmable

All fixtures:

