

Parkhurst

Graceful curves and bold angles combine to create a softly structured look in Parkhurst. An airy frame defines the form to produce unobstructed layers of light.

FINISHES

009 Brushed Nickel

31M Matte Black

109 Brushed Bronze



P500214-109

Parkhurst

P500371-109 Brushed Bronze
20" sq., 36" ht.
8 candelabra base, 60w max.



P500214-109 Brushed Bronze
14.37" sq., 24.37" ht.
4 candelabra base, 60w max.



P500213-109 Brushed Bronze
10.87" sq., 19.75" ht.
3 candelabra base, 60w max.



P400300-109 Brushed Bronze
42" L, 13" D, 15.12" ht.
6 candelabra base, 60w max.



Search the product number on progresslighting.com for full product details

Parkhurst

P400297-109 Brushed Bronze
30" dia., 14" ht.
6 candelabra base, 60w max.



P400296-109 Brushed Bronze
25.25" dia., 12.5" ht.
5 candelabra base, 60w max.



P400295-109 Brushed Bronze
21" dia., 12.25" ht.
3 medium base, 60w max.



P350255-109 Brushed Bronze
11.25" dia., 5.12" ht.
2 medium base, 15w max.



P710111-109 Brushed Bronze
7.5" W., 12" ht., 4" D.
2 medium base, 60w max.

ADA



P500361-109 Brushed Bronze
15.25" dia., 23.37" ht.
1 medium base, 60w max.



P500360-109 Brushed Bronze
11.5" dia., 16.75" ht.
1 medium base, 60w max.



FEATURED PRODUCT

Parkhurst

This dining room offers a calm and soothing ambiance from plenty of natural light, furniture fashioned from warm wood, and simple décor. The Parkhurst chandelier strikes a bright note as it combines a warm brushed bronze finish with graceful curves and bold angles, creating an airy structure that defines the form and produces unobstructed layers of light.

STYLE YOUR ROOM

Find inspiration for your next project on progresslighting.com

Parkhurst

P500371-31M Matte Black
20" sq., 36" ht.
8 candelabra base, 60w max.



P500214-031 Matte Black
14.37" sq., 24.37" ht.
4 candelabra base, 60w max.



P500213-031 Matte Black
10.87" sq., 19.75" ht.
3 candelabra base, 60w max.



P400300-31M Matte Black
42" L, 13" D, 15.12" ht.
6 candelabra base, 60w max.



Featuring Parkhurst

Parkhurst

Graceful curves and bold angles combine to create a softly structured look in Parkhurst. An airy frame defines the form to produce unobstructed layers of light.

FINISHES

009 Brushed Nickel

31M Matte Black

109 Brushed Bronze



P400296-31M

Parkhurst

P400297-31M Matte Black
30" dia., 14" ht.
6 candelabra base, 60w max.



P400296-31M Matte Black
25.25" dia., 12.5" ht.
5 candelabra base, 60w max.



P400295-31M Matte Black
21" dia., 12.25" ht.
3 medium base, 60w max.



P350255-31M Matte Black
11.25" dia., 5.12" ht.
2 medium base, 15w max.



P710111-31M Matte Black
7.5" W., 12" ht., 4" D.
2 medium base, 60w max.

ADA



P500361-31M Matte Black
15.25" dia., 23.37" ht.
1 medium base, 60w max.



P500360-31M Matte Black
11.5" dia., 16.75" ht.
1 medium base, 60w max.



Search the product number on progresslighting.com for full product details

Parkhurst

Graceful curves and bold angles combine to create a softly structured look in Parkhurst. An airy frame defines the form to produce unobstructed layers of light.

FINISHES

009 Brushed Nickel

31M Matte Black

109 Brushed Bronze



P500214-009

Parkhurst

P500371-009 Brushed Nickel
20" sq., 36" ht.
8 candelabra base, 60w max.



P500214-009 Brushed Nickel
14.37" sq., 24.37" ht.
4 candelabra base, 60w max.



P500213-009 Brushed Nickel
10.87" sq., 19.75" ht.
3 candelabra base, 60w max.



P400300-009 Brushed Nickel
42" L, 13" D, 15.12" ht.
6 candelabra base, 60w max.



Search the product number on progresslighting.com for full product details

Parkhurst

The Parkhurst pendant features a crisp dome metal shade suspended by an elegant ring. Light gleams softly from within, casting a soft glow on the surfaces below. This pendant is ideal for new traditional, modern farmhouse, and transitional interiors.

FINISHES

009 Brushed Nickel

31M Matte Black

109 Brushed Bronze



Parkhurst

P500367-009 Brushed Nickel
12.37" dia., 11.87" ht.
1 medium base, 100w max.



P500368-009 Brushed Nickel
17.87" dia., 15.25" ht.
3 medium base, 60w max.



P500367-31M Matte Black
12.37" dia., 11.87" ht.
1 medium base, 100w max.



P500368-31M Matte Black
17.87" dia., 15.25" ht.
3 medium base, 60w max.



P500367-109 Brushed Bronze
12.37" dia., 11.87" ht.
1 medium base, 100w max.



P500368-109 Brushed Bronze
17.87" dia., 15.25" ht.
3 medium base, 60w max.



Parkhurst

Graceful curves and bold angles combine to create a softly structured look in Parkhurst. An airy frame defines the form to produce unobstructed layers of light.

FINISHES

009 Brushed Nickel

31M Matte Black

109 Brushed Bronze



P400296-009

Parkhurst

P400297-009 Brushed Nickel
30" dia., 14" ht.
6 candelabra base, 60w max.



P400296-009 Brushed Nickel
25.25" dia., 12.5" ht.
5 candelabra base, 60w max.



P400295-009 Brushed Nickel
21" dia., 12.25" ht.
3 medium base, 60w max.



P350255-009 Brushed Nickel
11.25" dia., 5.12" ht.
2 medium base, 15w max.



P710111-009 Brushed Nickel
7.5" W., 12" ht., 4" D.
2 medium base, 60w max.

ADA



P500361-009 Brushed Nickel
15.25" dia., 23.37" ht.
1 medium base, 60w max.



P500360-009 Brushed Nickel
11.5" dia., 16.75" ht.
1 medium base, 60w max.



Search the product number on progresslighting.com for full product details

Parkhurst

009 Brushed Nickel

31M Matte Black

109 Brushed Bronze

P710111-009 Brushed Nickel
7.5" W., 12" ht., 4" D.
2 medium base, 60w max.



P710111-109 Brushed Bronze
7.5" W., 12" ht., 4" D.
2 medium base, 60w max.



P710111-31M Matte Black
7.5" W., 12" ht., 4" D.
2 medium base, 60w max.



All fixtures:



CLOSE-TO-CEILING

Parkhurst

Etched opal glass.

009 Brushed Nickel

31M Matte Black

109 Brushed Bronze

P350255-009 Brushed Nickel
11.25" dia., 5.12" ht.
2 medium base LED, 15w max.



P350255-31M Matte Black
11.25" dia., 5.12" ht.
2 medium base LED, 15w max.



P350255-109 Brushed Bronze
11.25" dia., 5.12" ht.
2 medium base LED, 15w max.

