

Paso







P250109-31M Matte Black 60" dia., 16.5" ht. Shown with Matte Black blades



Matte Black



P250109-031 Black 60" dia., 16.5" ht. Shown with Matte White blades



Matte White



P250109-163 Vintage Brass 60" dia., 16.5" ht. Shown with Matte White blades



Matte White



ENERGY INFORMATION

Airflow 5289 cubic feet per minute **Electricity Use** 33 watts (excludes lights) DOE Weighted CFM/W 174 CFM/W



Full Function Remote Control Included Six-speed fan operation Full-range dimming for light Reverse direction control

FEATURES

- Limited Lifetime Warranty
 Dual Mount (flat or sloped ceiling-20degree)
- DC Motor
- Damp Rated
- · Remote control with batteries included
- ABS Blades

All fixtures:

