

Schaal

028 Satin White 31M Matte Black

With a unique, wicker-wrapped shade and five reversible fan blades, the 52-inch Schaal ceiling fan brings a global presence to rooms in coastal settings. An 18W integrated LED module delivers soft, 3000K 90 CRI illumination through white opal glass. Schaal is offered in Matte White and Chestnut reversible blades with a Satin White housing or a Matte Black housing with Rustic Charcoal and Matte Black reversible blades. Its UL damp rating makes this lovely fan ideal for use inside or in outdoor covered areas. A full-function remote control and wall bracket are included.





Schaal

P250101-028-30 Satin White
52" dia., 16" ht.
*Shown with Chestnut blades
and Synthetic rope accent*

 Matte White
 Chestnut



P250101-31M-30 Matte Black
52" dia., 16" ht.
*Shown with Rustic Charcoal blades
and Synthetic rope accent*

 Rustic Charcoal
 Matte Black



ENERGY INFORMATION

Airflow 4,687 cubic feet per minute
Electricity Use 59 watts (excludes lights)
DOE Weighted CFM/W 89 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Reversible plywood blades
- White opal shade
- Damp Rated
- Remote control with batteries included

LAMPING

18w LED Module, 3000K, 90 CRI,
1600 source lumens, dimmable.

All fixtures:

