

Schaffer II

- 028 Satin White
- 31M Matte Black
- 081 Antique Nickel

Natural jute rope offers modern organic styling to the housing of the Schaffer four-blade ceiling fan, softening the housing's look and making it perfect for coastal and global spaces. This 52-inch ceiling fan has four reversible plywood blades offered in a choice of Classic Walnut and Grey Weathered Wood and an Antique Nickel housing, Matte Black and Rustic Charcoal with a Matte Black body, or Matte White and Natural Cherry and a Satin White housing. An 18W integrated LED module delivers soft, 3000K 90 CRI illumination through white opal glass. Its UL damp rating makes this lovely fan ideal for use inside or in outdoor covered areas. A 3-speed remote control and wall bracket are included.



Schaffer II

P250097-028-30 Satin White
56" dia., 15.5" ht.
*Shown with Natural Cherry blades
and Natural Jute rope accent*

- Matte White
- Natural Cherry



P250097-31M-30 Matte Black
56" dia., 15.5" ht.
*Shown with Rustic Charcoal blades,
Natural Jute rope accent and light kit
removed using blank plate*

- Rustic Charcoal
- Matte Black



P250097-081-30 Antique Nickel
56" dia., 15.5" ht.
*Shown with Classic Walnut blades
and Natural Jute rope accent*

- Classic Walnut
- Grey Weathered Wood



ENERGY INFORMATION

Airflow 6,177 cubic feet per minute
Electricity Use 67 watts (excludes lights)
DOE Weighted CFM/W 98 CFM/W



Three-speed Remote Control Included
*Three-speed fan operation
Full-range dimming for light*

FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Damp Rated
- Remote control with batteries included
- Remote control may be replaced with P2630-30 wall control
- Add the P2667-31 WiFi remote control

LAMPING

18w LED Module, 3000K, 90 CRI,
1600 source lumens, dimmable.

All fixtures:

