

Shear

31M

Matte Black

109

Brushed Bronze

P250115-31M-30 Matte Black
19.63" dia., 17.75" ht.



P250115-109-30 Brushed Bronze
19.63" dia., 17.75" ht.



ENERGY INFORMATION*

Airflow N/A
Electricity Use N/A
DOE Weighted CFM/W N/A

**Data not available at time of printing*



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- 360° Oscillation
- Limited Lifetime Warranty
- DC Motor
- Damp Rated
- Remote Control with Batteries Included
- Edge lit LEDs
- Rust Proof Blades

LAMPING

31W LED Strip, 3000K, 90 CRI,
1700 Source Lumens, dimmable

All fixtures:

