

Springer II

31M Matte Black 081 Antique Nickel 129 Architectural Bronze

Relax under the refreshing breeze of the Springer Collection 60-Inch Windmill Ceiling Fan. Its large scale and windmill-style blades make it ideal for any great room, bedroom, living room, or bonus room in modern farmhouse, rustic, and coastal-style settings. Its twelve sweeping blades are coated in a choice of Distressed Charcoal with a Matte Black housing, Antique Nickel with Galvanized blades, and Distressed Walnut finished blades with an Architectural Bronze body for a rustic flair. Its cULus damp rating makes this lovely fan ideal for use inside or in outdoor covered areas. A full-function remote control and wall bracket are included.



P250098-31M

Springer II

P250098-31M Matte Black
60" dia., 16.26" ht.
Shown with Distressed Charcoal blades

Distressed Charcoal



P250098-081 Antique Nickel
60" dia., 16.26" ht.
Shown with Galvanized blades

Galvanized




P250098-129 Architectural Bronze
60" dia., 16.26" ht.
Shown with Distressed blades

Distressed Walnut



ENERGY INFORMATION

Airflow	6,158 cubic feet per minute
Electricity Use	35 Watts (excludes lights)
DOE Weighted CFM/W	205 CFM/W



FEATURES

- Limited Lifetime Warranty
- DC Motor
- Hand painted aluminum blades
- Damp Rated
- Remote control with batteries included
- Add the P2673 WiFi remote

ALSO IN: LIGHT KITS



All fixtures:



Springer II

31M Matte Black

081 Antique Nickel

129 Architectural Bronze

P260004-31M-WB Matte Black

P260004-081-WB Antique Nickel

P260004-129-WB Architectural Bronze

12" dia., 11" ht.

2 medium base, 7w LED.

Only for use with P250000,

P250065 and P250098.

All fixtures:

