

# Tarsus

009 Brushed Nickel 31M Matte Black



A clean, modern design and color-selectable LED technology give the Tarsus 52-inch ceiling fan high function and a distinctive style. This fan illuminates indoor contemporary spaces with 25W integrated LED light source. Choose from a gentle 2700K, 3000K soft light or a bright 5000K light on the included full-function remote control. Five reversible plywood blades are finished in a choice of Silver and Chestnut with a Brushed Nickel housing or Matte Black and Rustic Charcoal with a Matte Black housing. Its DC motor is UL rated for indoor use and operates with whisper-quiet efficiency.



P250102-31M-CS



# Tarsus

**P250102-009-CS** Brushed Nickel  
52" dia., 14.75" ht.  
*Shown with Chestnut blades*

 Silver  
 Chestnut



**P250102-31M-CS** Matte Black  
52" dia., 14.75" ht.  
*Shown with Rustic Charcoal blades*

 Rustic Charcoal  
 Matte Black



**3-CCT** SELECTABLE  
2700K  
3000K  
5000K

### ENERGY INFORMATION

**Airflow** 4,950 cubic feet per minute  
**Electricity Use** 60 watts (excludes lights)  
**DOE Weighted CFM/W** 94 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Full-range dimming for light  
Reverse direction control

### FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included

### LAMPING

25w LED Module, 90 CRI + 10w Linear LED Module, 80 CRI, 2700K, 3000K, 5000K, 2000 source lumens, dimmable.

All fixtures:

