



### Specifications

- Cable supported:  
F/FTP, S/FTP, F/UTP and UTP  
Cable jacket O.D. 0.236–0.315" (6–8mm)
- Conductor:  
Solid: 22–26AWG
- Performance:  
ANSI/TIA-568-C.2 Category 6A and Category 6 channel
- Full 802.3bt (4PPoE) support, Type 3 and 4
- UL Plenum rated

## NEXTSPEED® COBRA-LOCK™ Field Termination Plugs

Description	Catalog No.
Category 6A	<b>SP6A</b>
Category 6	<b>SP6</b>
Category 6A	<b>SC6A</b>
Category 6A	<b>SCP6A</b>



## Jack Accessories

### Jack Dust Covers, XJ and HJ Series

Description	Catalog No.
Polypropylene, clear, 25-pack	<b>HXJDC25</b>



*Note: Mounts within the icon slots located above the RJ45 opening. Cannot be used with SJ shielded jack series.*

### Secure-IT RJ-45 Port Blocker

Physically lock out access to individual RJ-45 ports with the Secure-IT Port Blocker. Compatible with any RJ-45 port, the blocker inserts easily and requires the supplied tool to remove.

Description	Catalog No.
Locking RJ-45 port blocker	<b>RJ45PB50</b>



*Note: Fits any RJ-45 port*

### Secure-IT Plug Lock Kit

Components for Secure-IT plugs used on BIDNet plugs and Secure-IT patch cords

Description	Catalog No.
Plug lock kit	<b>BCSPKT12</b>

*Note: Includes both tamper resistant and locking components with one removal tool.*



### Jack Icons, XJ and HJ Series

100-pack, snaps onto jack nose

	Blank	Computer	Telephone
Color	Catalog No.	Catalog No.	Catalog No.
Black	<b>IBK100</b>	<b>IBK100C</b>	<b>IBK100T</b>
Blue	<b>IB100</b>	<b>IB100C</b>	<b>IB100T</b>
Brown	<b>IBN100</b>	<b>IBN100C</b>	<b>IBN100T</b>
Gray	<b>IGY100</b>	<b>IGY100C</b>	<b>IGY100T</b>
Green	<b>IGN100</b>	<b>IGN100C</b>	<b>IGN100T</b>
Ivory	<b>IEI100</b>	<b>IEI100C</b>	<b>IEI100T</b>
Orange	<b>IOR100</b>	<b>IOR100C</b>	<b>IOR100T</b>
Purple	<b>IP100</b>	<b>IP100C</b>	<b>IP100T</b>
Red	<b>IR100</b>	<b>IR100C</b>	<b>IR100T</b>
White	<b>IW100</b>	<b>IW100C</b>	<b>IW100T</b>
Yellow	<b>IY100</b>	<b>IY100C</b>	<b>IY100T</b>

*Note: Cannot be used with SJ shielded jack series; custom icon numbering and labeling available; contact Customer Service for details*

See color chart on page B2