



Specifications

- Cold rolled steel
- H3N cabinets: 12 gauge rails; 22 gauge sides
- H3S cabinets: 14 gauge rails; 22 gauge sides
- Black powder coated
- Integrated swing handle lock on doors
- Casters and leveling feet installed
- 3,080lb weight rating
- Locks on side covers
- One vertical cable manager included
- Rail depth markings

Standards

- UL 2416
- EIA-310-E hole spacing

H3 Network Cabinets

| RU | Height | Width | Depth | Rail | Catalog No. |
|----|--------|-------|-------|-----------------|----------------|
| 42 | 76.6" | 31.2" | 43" | #12-24 threaded | H3N4242 |
| | | | 49" | #12-24 threaded | H3N4248 |
| 47 | 85.3" | 31.2" | 43" | #12-24 threaded | H3N4742 |
| | | | 49" | #12-24 threaded | H3N4748 |

H3 Server Cabinets

| RU | Height | Width | Depth | Rail | Catalog No. |
|----|--------|-------|-------|-------------|----------------|
| 42 | 76.6" | 23.6" | 43" | M6 cage nut | H3S4242 |
| | | | 49" | M6 cage nut | H3S4248 |
| 47 | 85.3" | 23.6" | 43" | M6 cage nut | H3S4742 |
| | | | 49" | M6 cage nut | H3S4748 |

H3 Fan Trays

| CFM | Amp Draw | Voltage | Catalog No. |
|-----|----------|---------|----------------|
| 162 | 0.23A | 110V | H3FT110 |
| 162 | 0.11A | 230V | H3FT230 |

Cage Nut Rails for H3N Cabinets

| Compatibility | Height | Rail | Catalog No. |
|----------------------|--------|------------|---------------|
| H3N network cabinets | 42U | M6 cagenut | H3NR42 |
| | 47U | M6 cagenut | H3NR47 |

Vertical Cable Managers

| Compatibility | Height | Catalog No. |
|---------------|--------|---------------|
| H3S or H3N | 42U | H3CM42 |
| | 47U | H3CM47 |