

TRP1/RDI1/QSP1

GeoPak Architectural Wallpacks

LED WALLPACKS

NEW



Small sized architectural wallpacks in three stylish shapes accentuate building architecture and provide excellent illumination and uniformity

- Back box accessory available for surface conduit application
- Die-cast aluminum with a hinged back-plate for ease of installation and maintenance.
- The LED bezel and trim-plate are made of stainless steel
- Wet Location Listed to UL924 and UL1598 Standard
- 0-10V dimming driver standard
- 10kA surge protector
- Universal spider plate for mounting to standard 3 1/2" and 4" square electrical boxes

- Zero uplight (U0), dark sky, neighbor friendly optics
- Drivers IP66 and RoHS compliant

• DesignLights Consortium® (DLC) qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org

Battery Backup:

- Optional Battery Backup provides emergency lighting for the required 90 minute path of egress
- Includes a long-life Lithium Iron Phosphate battery and optional battery heater for cold temperature application
- Spectron® self-testing/self-diagnostic electronics are included standard

MADE-TO-ORDER ORDERING INFORMATION

HOUSING/FAMILY	VERSION	WATTAGE	CCT	DISTRIBUTION	VOLTAGE	FINISH	CONTROL OPTIONS	OPTIONS
TRP1 Trapezoid	12L 12 LEDs	15 15 watts	3K7 3000K, 70CRI	2 Type II	U 120V-277V	BL Black	PCU Button Photocontrol	F ⁴ Fusing
RDI1 Radius		20 20 watts	4K7 4000K, 70CRI	3 Type III	1 120V	DB Bronze	SCP ^{2,3} Programmable motion sensor	E ¹ Battery Pack (0° C)
QSP1 Qtr-Sphere		30 30 watts	5K7 5000K, 70CRI	4 Type IV	2 208V 3 240V 4 277V	GR Gray PS Platinum WH White CC Custom Color		EH ¹ Battery Pack (-30° C) with heater
							SPEC SCP MOUNT HT.	
							8F Up to 8ft mount height	
							20F Up to 20ft mount height	

¹ Voltage specific (120 or 277V only)
² Must order minimum of one remote control to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings, 120-277V only
³ PCU option not applicable, included in sensor
⁴ Must specify input voltage (120, 208, 240 or 277)

ACCESSORIES (ORDER SEPARATELY)

Catalog Number	Description
SCP-REMOTE	Remote control for SCP option. Order at least one per project to program and control dimming settings
BB-GEO-XX	Black box with 4 - 1/2" threaded conduit holes, specify finish by replacing "XX" with finish selection, eg. Dark Bronze "DB"

PERFORMANCE INFORMATION

Series Number	Equivalency			Energy Savings	Delivered Lumens	System Watts	Lumens Per Watt	Mounting Height	CCT	Voltage	Drivers/Current
	MH	HPS	CFL								
TRP/RDI/QSP1-12L-15-4K	70w	70w	42w	84%	1,600	14	113	7-12 ft.	4000K	120-277V	1@350mA
TRP/RDI/QSP1-12L-20-4K	100w	100w	2x32w	84%	2,200	20	109	8-14 ft.	4000K	120-277V	1@500mA
TRP/RDI/QSP1-12L-30-4K	150w	150w	2x42w	84%	2,900	28	102	9-16 ft.	4000K	120-277V	1@700mA

DIMENSIONS

