




15 and 20 Ampere, 125 and 250 Volts




HBL8600I




HBL5262



HBL5362IWR



HBL5261



HBL5284

Dimensions in Inches (mm)

HBL® Extra Heavy Duty Max Hospital Grade Receptacles



15A 250V
NEMA 6-15R
UL CSA
1.5 HP



20A 250V
NEMA 6-20R
UL CSA
2 HP

Duplex	Color	Catalog Number	
Flush, thermoplastic polyester face, back and side wired.	Brown	HBL8600	HBL8400
	Ivory	HBL8600I	HBL8400I

Note: See page A-48 for accessories.
See section N for wallplates.



15A 125V
NEMA 5-15R
UL CSA
0.5 HP



20A 125V
NEMA 5-20R
UL CSA
1 HP

HBL® Extra Heavy Duty Max Specification Grade Receptacles

Duplex	Color	Catalog Number		
Flush, nylon face, back and side wired.	Black	HBL5262BK	HBL5362BK	
	Blue	—	HBL5362BL	
	Brown	HBL5262	HBL5362	
	Gray	HBL5262GY	HBL5362GY	
	Ivory	HBL5262I	HBL5362I	
	Red	HBL5262R	HBL5362R	
	White	HBL5262W	HBL5362W	
	Isolated ground ^A .	Gray	IG5262GY	IG5362GY
		Ivory	IG5262I	IG5362I
		Orange	IG5262	IG5362
Non-isolated ground, bulk pack of 100.	Red	IG5262R	IG5362R	
	White	—	IG5362W	
	Orange	—	HBL5362M4	
	Weather Resistant, flush, nylon face, back and side wired.	Black	HBL5262BKWR	HBL5362BKWR
		Brown	HBL5262WR	HBL5362WR
Gray		HBL5262GYWR	HBL5362GYWR	
Ivory		HBL5262IWR	HBL5362IWR	
Red		HBL5262RWR	HBL5362RWR	
Corrosion resistant.	White	HBL5262WWR	HBL5362WWR	
	Ivory	HBL52CM62I	—	
Weather Resistant, Isolated ground ^A .	Yellow	HBL52CM62	HBL53CM62	
	Gray	IG5262GYWR	IG5362GYWR	
	Ivory	IG5262IWR	IG5362IWR	
	Orange	IG5262WR	IG5362WR	
	Red	IG5262RWR	IG5362RWR	
On 4 in. (101.6) round cover.	White	—	IG5362WWR	
	Brown	HBL5282	—	

Single

Flush, nylon face, back and side wired.	Black	HBL5261BK	HBL5361BK
	Brown	HBL5261	HBL5361
	Gray	—	HBL5361GRY
	Ivory	HBL5261I	HBL5361I
	White	—	HBL5361W
Isolated ground ^A .	Orange	IG5261	IG5361
Weather Resistant, Isolated ground ^A .	Orange	IG5261WR	IG5361WR
Ring terminal connection.	Brown	HBL5261RT	HBL5361RT
	White	HBL5261WRT	—
	Yellow	HBL5261YRT	—
Weather Resistant, flush, nylon face, back and side wired.	Brown	HBL5261WR	HBL5361WR
	Gray	—	HBL5361GRYWR
Corrosion resistant.	Ivory	HBL5261IWR	HBL5361IWR
	Yellow	HBL52CM61	HBL53CM61
Panel mount on 1.94 in. (49.3) centers.	Brown	HBL5284	HBL5357

Note: ^ASee section N for additional information on isolated ground devices.

See pages A-47 and A-48 for accessories.

See page Tech-10 for Weather Resistant descriptions.

See section O for wallplates.