


Straight Blade Devices

15 and 20 Ampere, 125 Volts

IP20
SUITABILITY



HBL5262STWWR

EdgeConnect™ HBL® Extra Heavy Duty Specification Grade Receptacles

Weather Resistant,
Finder Groove Face,
Spring Termination



Black
Blue
Brown
Gray
Green
Ivory
Light Almond
Orange
Red
White

HBL5262STBKWR
HBL5262STBLWR
HBL5262STWWR
HBL5262STGYWR
HBL5262STGNWR
HBL5262STIWR
HBL5262STLAWR
HBL5262STOWR
HBL5262STRWR
HBL5262STWWR

HBL5362STBKWR
HBL5362STBLWR
HBL5362STWWR
HBL5362STGYWR
HBL5362STGNWR
HBL5362STIWR
HBL5362STLAWR
HBL5362STOWR
HBL5362STRWR
HBL5362STWWR

EdgeConnect™ Hubbell-PRO Extra Heavy Duty Specification Grade Receptacles

Weather Resistant,
Finder Groove face, duplex,
spring termination



Black
Blue
Brown
Gray
Green
Ivory
Light Almond
Orange
Red
White

5262STBKWR
5262STBLWR
5262STWWR
5262STGYWR
5262STGNWR
5262STIWR
5262STLAWR
5262STOWR
5262STRWR
5262STWWR

5362STBKWR
5362STBLWR
5362STWWR
5362STGYWR
5362STGNWR
5362STIWR
5362STLAWR
5362STOWR
5362STRWR
5362STWWR



DR20STWWR

EdgeConnect™ Commercial Specification Grade Receptacles

Weather Resistant,
Smooth face, duplex,
spring termination



Black
Blue
Brown
Gray
Green
Ivory
Light Almond
Orange
Red
White

BR15STBKWR
BR15STBLWR
BR15STWWR
BR15STGYWR
BR15STGNWR
BR15STIWR
BR15STLAWR
BR15STOWR
BR15STRWR
BR15STWWR

BR20STBKWR
BR20STBLWR
BR20STWWR
BR20STGYWR
BR20STGNWR
BR20STIWR
BR20STLAWR
BR20STOWR
BR20STRWR
BR20STWWR



DR15STIWRTR

Weather Resistant,
Tamper-Resistant,
smooth face, duplex,
spring termination



Black
Blue
Brown
Gray
Green
Ivory
Light Almond
Orange
Red
White

BR15STBKWRTR
BR15STBLWRTR
BR15STWWRTR
BR15STGYWRTR
BR15STGNWRTR
BR15STIWRTR
BR15STLAWRTR
BR15STOWRTR
BR15STRWRTR
BR15STWWRTR

BR20STBKWRTR
BR20STBLWRTR
BR20STWWRTR
BR20STGYWRTR
BR20STGNWRTR
BR20STIWRTR
BR20STLAWRTR
BR20STOWRTR
BR20STRWRTR
BR20STWWRTR

Weather Resistant,
Style Line® decorator duplex,
spring termination



Black
Blue
Brown
Gray
Green
Ivory
Light Almond
Orange
Red
White

DR15STBKWR
DR15STBLWR
DR15STWWR
DR15STGYWR
DR15STGNWR
DR15STIWR
DR15STLAWR
DR15STOWR
DR15STRWR
DR15STWWR

DR20STBKWR
DR20STBLWR
DR20STWWR
DR20STGYWR
DR20STGNWR
DR20STIWR
DR20STLAWR
DR20STOWR
DR20STRWR
DR20STWWR



BR15STGYWR

Weather Resistant,
Tamper-Resistant,
Style Line® decorator duplex,
spring termination



Black
Blue
Brown
Gray
Green
Ivory
Light Almond
Orange
Red
White

DR15STBKWRTR
DR15STBLWRTR
DR15STWWRTR
DR15STGYWRTR
DR15STGNWRTR
DR15STIWRTR
DR15STLAWRTR
DR15STOWRTR
DR15STRWRTR
DR15STWWRTR

DR20STBKWRTR
DR20STBLWRTR
DR20STWWRTR
DR20STGYWRTR
DR20STGNWRTR
DR20STIWRTR
DR20STLAWRTR
DR20STOWRTR
DR20STRWRTR
DR20STWWRTR

Dimensions in Inches (mm)