


Straight Blade Devices

Miscellaneous and Combination Receptacles

2 Pole, 3 Wire Grounding



Miscellaneous Receptacles

Description	Catalog Number
Receptacle, display type, brown phenolic with .060 in. brass plate and blank flush plug.	HBL5236
Replacement receptacle for HBL5236.	HBL5236M2
Replacement threaded plug for HBL5236.	HBL5236PLUG*
Receptacle, wooden floors, brown phenolic with .060 in. brass plate, blank flush plug and box.	HBL6236
Receptacle, clock hanger, white with stainless steel plate.	HBL5235













HBL5236




HBL5235

Special Combination Duplex Receptacles

Description	Catalog Number
15A, 125V Brown RTP, 1 feed, 1 return, back/side wired	HBL4792
 Brown RTP, 2 feeds, 1 return, side wired	HBL4794
15A, 125V  Brown RTP, 2 feeds, 2 returns, side wired	HBL4795
15A, 250V  Brown nylon face, 2 circuit, back and side wired	HBL5292
15A, 125V  Ivory nylon face, 2 circuit, back and side wired	HBL52921
20A, 250V  Brown nylon face, 2 circuit, back and side wired	HBL5492
20A, 125V  Ivory nylon face, 2 circuit, back and side wired	HBL54921
15A, 125V  Brown RTP, 2 feeds, 1 return, common ground	HBL7371
10A, 250V 15A, 125V  Brown nylon, side and back wired	HBL5392
20A, 125V  Note: This device will only accept 20A grounding plugs.	



HBL4792



HBL5292

Note: RTP is an abbreviation for reinforced thermoplastic polyester.

*Not UL Listed or CSA certified.

See page A-47 for accessories.

Dimensions in Inches (mm)