

# Straight Blade Devices

## Accessories

For 15 and 20 Ampere, 125 and 250 Volts and 277 Volts AC Devices



### Wallplates, 1-Gang

Description	Color	Duplex Receptacle	Style Line® Receptacle	Single Receptacle Plate 1.40 in. (35.6) Dia.
Thermoplastic, smooth.	Black	<b>P8BK</b>	<b>P26BK</b>	<b>P7BK</b>
	Brown	<b>P8</b>	<b>P26</b>	<b>P7</b>
	Gray	<b>P8GY</b>	<b>P26GY</b>	<b>P7GY</b>
	Ivory	<b>P8I</b>	<b>P26I</b>	<b>P7I</b>
	Light Almond	<b>P8LA</b>	<b>P26LA</b>	<b>P7LA</b>
	Orange	<b>P8OR</b>	–	–
	Red	<b>P8R</b>	<b>P26R</b>	<b>P7R</b>
	White	<b>P8W</b>	<b>P26W</b>	<b>P7W</b>
	Stainless steel 302/304, .035 in. (0.9) horizontal brushed finish.		<b>SS8</b>	<b>SS26</b>
Brass .04 in. (1.0), horizontal brushed finish.		<b>SB8</b>	<b>SB26</b>	<b>SB7</b>
Aluminum .05 in. (1.3), horizontal brushed finish.		<b>SA8</b>	–	<b>SA7</b>



**P8**



**P26I**



**SS7**

### Weatherproof Covers

Description	Duplex Receptacle	Single Receptacle Plate 1.40 in. (35.6) Dia.
RTP, gray, for FS/FD box mounting.	<b>HBL5221</b>	<b>HBL7423WO</b>
RTP, yellow, for FS/FD box mounting.	<b>HBL52CM21</b>	<b>HBL74CM23WO</b>
RTP, gray, for device mounting.	<b>HBL5222</b>	–
RTP, yellow, for device mounting.	<b>HBL52CM22</b>	–
Cast aluminum for FS/FD box mounting.	<b>HBL5206WO</b>	<b>HBL7420</b>
Cast aluminum for device mounting.	<b>HBL5205WO</b>	–

Note: All weatherproof plates are UL Listed for Wet Locations.  
 Those with suffix WO are listed for use with cover open, all others with cover closed.  
 RTP is an abbreviation for reinforced thermoplastic polyester.  
 See section O for additional information on cover plates.



**HBL52CM22**



**HBL5206WO**



**HBL7423WO**

Dimensions in Inches (mm)