

15 and 20 Amp Receptacles

Style Line® Decorator Receptacles

- High-impact nylon face resists breaking, chipping and cracking.
- Will accept locking fork terminal to comply with ABYC standards.
- Available in 4 colors for any decor with matching wall plates.
- Smooth, high-gloss finish for rich appearance.

Commercial Style Line® Decorator Series



Description	Color	Standard Duplex	Duplex, Tamper-Resistant	Duplex, Weather and Tamper-Resistant
15A 125V duplex receptacle.	Black	DR15BLK	DR15BLKTR	DR15BLKWTRTR
	Brown	DR15	DR15TR	DR15WRTR
	Gray	DR15GRY	DR15GRYTR	DR15GRYWTRTR
	Ivory	DR15I	DR15ITR	DR15IWTRTR
	Light Almond	DR15LA	DR15LATR	DR15LAWTRTR
	White	DR15WHI	DR15WHITR	DR15WHIWTRTR



DR15ITR



DR15GRYWTRTR

Commercial Series



Description	Color	Standard Duplex, Spec. Grade, Side Wired	Duplex, Tamper-Resistant	Duplex, Weather and Tamper-Resistant, Back and Side Wired
15A 125V duplex receptacle.	Black	CR15BLK	CR15BLKTR	BR15BLKWTRTR
	Brown	CR15	CR15TR	BR15WRTR
	Gray	CR15GRY	CR15GRYTR	BR15GRYWTRTR
	Ivory	CR15I	CR15ITR	BR15IWTRTR
	Light Almond	CR15LA	CR15LATR	BR15LAWTRTR
	White	CR15WHI	CR15WHITR	BR15WHIWTRTR



CR15TR



BR15IWTRTR

Note: All devices above will accept locking fork terminal to comply with ABYC standards. See page Tech-10 for Tamper and Weather Resistant descriptions.

Extra Heavy Duty Single Receptacles

Description	Color	Catalog Number
15A 125V single receptacle.	Brown	HBL5251
	Ivory	HBL5251I
20A 125V single receptacle.	Brown	HBL5361
	Ivory	HBL5361I



HBL5251



HBL5361I

Corrosion-Resistant Receptacles



Description	Color	Catalog Number
15A 125V yellow corrosion-resistant duplex receptacle. Use where salt or other corrosive elements are a problem.	Yellow	HBL52CM62
Same as HBL52CM62 except ivory in color.	Ivory	HBL52CM62I



HBL52CM62I



HBL8200II

Special Application Illuminated Receptacle

Description	Color	Catalog Number
Illuminated receptacle 15A 125V grounding. A high quality receptacle with an illuminated face. Ideal for use in halls or as a gentle night light.	Ivory	HBL8200II

Note: See page Tech-10 for Weather Resistant description.