











Wallplates

Non-metallic Plates

- High-impact polycarbonate thermoplastic is virtually unbreakable
- Smooth satin finish, blends into the wall
- Screws are factory-inserted for fumble-free installation

Stainless Steel Plates

- Type 302/304
- Non-magnetic
- Ideal for highly corrosive environments

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
 1-Gang, 1-Toggle	Black Brown Gray Ivory White	P1BK P1 P1GY P1I P1W	PJ1BK PJ1 PJ1GY PJ1I PJ1W	Brass Stainless Steel	SB1 SS1
 1-Gang, 1-Duplex	Black Brown Gray Ivory White	P8BK P8 P8GY P8I P8W	PJ8BK PJ8 PJ8GY PJ8I PJ8W	Brass Stainless Steel	SB8 SS8
 1-Gang, 1-Decorator	Black Brown Gray Ivory White	P26BK P26 P26GY P26I P26W	PJ26BK PJ26 PJ26GY PJ26I PJ26W	Brass Stainless Steel	SB26 SS26
 2-Gang, 2-Toggle	Black Brown Gray Ivory White	P2BK P2 P2GY P2I P2W	PJ2BK PJ2 PJ2GY PJ2I PJ2W	Brass Stainless Steel	SB2 SS2
 2-Gang, 2-Duplex	Black Brown Gray Ivory White	P82BK P82 P82GY P82I P82W	PJ82BK PJ82 PJ82GY PJ82I PJ82W	Brass Stainless Steel	SB82 SS82
 2-Gang, 2-Decorator	Black Brown Gray Ivory White	P262BK P262 P262GY P262I P262W	PJ262BK PJ262 PJ262GY PJ262I PJ262W	Brass Stainless Steel	SB262 SS262
 2-Gang, 1-Toggle, 1-Duplex	Black Brown Gray Ivory White	– P18 P18GY P18I P18W	PJ18BK PJ18 PJ18GY PJ18I PJ18W	Brass Stainless Steel	SB18 SS18
 2-Gang, 1-Toggle, 1-Decorator	Black Brown Gray Ivory White	P126BK P126 P126GY P126I P126W	PJ126BK PJ126 PJ126GY PJ126I PJ126W	Brass Stainless Steel	SB126 SS126
 1-Gang, 1-Single 1.40" Dia. Hole	Black Brown Gray Ivory White	P7BK P7 P7GY P7I P7W	PJ7BK PJ7 PJ7GY PJ7I PJ7W	Brass Stainless Steel	SB7 SS7
 1-Gang, 1-Blank, Box Mount	Black Brown Gray Ivory White	P13BK P13 P13GY P13I P13W	PJ13BK PJ13 PJ13GY PJ13I PJ13W	Brass Stainless Steel	SB13 SS13