


**30 Amp, 3ØY 120/208, 277/480 and 347/600 Volts AC
4 Pole, 5 Wire, Grounding**



HBL2811SW




HBL2811S



HBL2811



HBL2815SW



HBL2815

Dimensions in Inches (mm)



**30A 3ØY
120/208V AC
NEMA L21-30P
3 HP**



**30A 3ØY
240/415V AC
NEMA L26-30P**



**30A 3ØY
277/480V AC
NEMA L22-30P
10 HP**



**30A 3ØY
347/600V AC
NEMA L23-30P**

Plugs

Watertight Safety-Shroud®

IP66 SUITABILITY

UL Type 4x, 12

Description	Cord Dia.	Catalog Number			
Black Valox® housing, white Valox® clamps.	.350"-1.150" (9-29)	HBL2811SW	HBL2801	HBL2821SW	HBL2831SW

Safety-Shroud®

IP20 SUITABILITY

Description	Cord Dia.	Catalog Number			
Black and white nylon body, white Valox® shroud. Can be used with the Insulgrip Connector Bodies.	.350"-1.150" (9-29)	HBL2811S	-	-	-

Note: See page B-52 for accessories.

Insulgrip®

IP20 SUITABILITY

Description	Cord Dia.	Catalog Number			
Black and white nylon.	.350"-1.150" (9-29)	HBL2811	-	HBL2821	HBL2831
Black and white nylon, spring termination.	.350"-1.150" (9-29)	HBL2811ST	-	HBL2821ST	-
Corrosion resistant, yellow nylon.	.350"-1.150" (9-29)	HBL28CM11	-	-	-
Black and white for flat cable.	.350"-1.150" (9-29)	HBL2811FC	-	-	-
All black nylon.	.350"-1.150" (9-29)	HBL2811BK	-	-	-
All black nylon, spring termination.	.350"-1.150" (9-29)	HBL2811STBK	-	-	-

Note: See page B-52 for accessories.

Flanged Inlets

Watertight Safety-Shroud®

IP66 SUITABILITY

UL Type 4x, 12

Description	Catalog Number		
Gray Valox® housing and flange.	HBL2815SW	HBL2805	-

Note: See page B-54 for accessories.

Insulgrip®

IP20 SUITABILITY

Description	Catalog Number			
Nylon casing, back wired.	HBL2815	-	HBL2825	HBL2835
Nylon casing, spring termination.	HBL2815ST	-	HBL2825ST	-

Note: See page B-52 for accessories.

See pages B-69 and B-70 for technical information on Twist-Lock and Watertight Safety-Shroud devices.

Twist-Lock® 3-Phase Circuit Tester



Description	Rating	Catalog Number			
3-Phase Circuit Tester	3Ø 120/208V AC Min. Voltage: 90V AC	HBL3PT2811	-	-	-

Note: Testers in other NEMA configurations can be developed upon request.

See page B-53 for additional circuit testers.



HBL3PT2811

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.

HBLMITL - For use with Watertight Safety-Shroud receptacles, see page B-41.

