

## 30 Amp, 3ØY 120/208, 277/480 and 347/600 Volts AC 4 Pole, 4 Wire, Non-Grounding

**IP20**  
SUITABILITY



30A 3ØY 120/208V AC  
NEMA L18-30P  
3 HP


30A 3ØY 277/480V AC  
NEMA L19-30P  
10 HP

30A 3ØY 347/600V AC  
NEMA L20-30P

### Plugs

Description	Cord Dia.	Catalog Number
Black and white nylon.	.350"-1.150" (9-29)	<b>HBL2751</b> <b>HBL2761</b> <b>HBL2771</b>

Note: See page B-53 for accessories.



**HBL2751**

### Flanged Inlets

Description	Catalog Number
Nylon casing, back wired.	<b>HBL2755</b> <b>HBL2765</b> <b>HBL2775</b>

Note: See page B-52 for accessories.

**IP20**  
SUITABILITY



30A 3ØY 120/208V AC  
NEMA L18-30R  
3 HP


30A 3ØY 277/480V AC  
NEMA L19-30R  
10 HP

30A 3ØY 347/600V AC  
NEMA L20-30R

### Connector Bodies

Description	Cord Dia.	Catalog Number
Black and white nylon.	.350"-1.150" (9-29)	<b>HBL2753</b> <b>HBL2763</b> <b>HBL2773</b>

Note: See page B-52 for accessories.



**HBL2755**




**HBL2753**

### Single Flush Receptacles

Description	Catalog Number
Black nylon face, back and side wired.	<b>HBL2750</b> <b>HBL2760</b> <b>HBL2770</b>

Note: See page B-52 for accessories.




**HBL2750**

### Flanged Receptacles

Description	Catalog Number
Nylon casing, back wired.	<b>HBL2756</b> <b>HBL2766</b> <b>HBL2776</b>

Note: See page B-52 for accessories.

See page B-69 for technical information on Twist-Lock devices.



**HBL2756**

Dimensions in Inches (mm)