

Twist-Lock® Devices

Miniature 20 & 25 Amp Power Connections for Entertainment Applications



Insul-Lock™ Plus Inline Connectors

Description	Male Connector Power In	Female Connector Power Out
20 Amp locking cable connector, screw terminals	HBLMC	HBLFC

Insul-Lock™ Plus Panel Mounts

Description	Inlet	Outlet
20 Amp ¼" tab terminations without divider	HBLMP	HBLFP
20 Amp ¼" tab terminations, with divider	HBLMPD	HBLFPD

Insul-Lock™ Plus Accessories

Description	Inlet	Outlet
Spring loaded watertight cover	HBLMPC	HBLFPC
Watertight dust protection cap with chain	HBLMPDC	HBLFPDC

Insul-Lock™ Plus Certifications

UL Recognized component for USA and Canada
Connectors are rated UL50E Enclosure type 4X when used with mating connector or with panel mount and watertight cover.

Panel Mounts are rated UL50E Enclosure type 4X with the cover closed or with the mating connectors.
IP65 Rated

Rated for connection and disconnection under load.



Insul-Lock™ Inline Connectors

Description	Male Connector Power In (Blue)	Female Connector Power Out (Gray)
25 Amp locking cable connector, screw terminals	HBLCPIBL	HBLCPOGY

Insul-Lock™ Panel Mounts

Style	Power In (Blue)	Power Out (Gray)
25 Amp ¼" tab terminations without divider	HBLPMIBL	HBLPMOGY
25 Amp ¼" tab terminations with divider	HBLPMIDBL	HBLPMODGY

Insul-Lock™ Accessories

Description	Catalog Number
Panel mount retainer plate (also compatible with HBLMP & HBLMPD)	HBLPMRP
Panel mount M3x.5 screw, 8mm long	HBLPMSC

Insul-Lock™ Certifications

UL Recognized component for USA and Canada
VDE Certified

Do not connect or disconnect under load.

Dimensions in Inches (mm)