



### UL Type 4X Watertight Lift Covers



HBL6500

	Description	Color	Lift Cover
Lift Cover Assembly	For use with 15A or 20A straight blade receptacles and 15A Twist-Lock® receptacles; receptacle not included.	Yellow Black	<b>HBL6500</b> <b>HBL6500BK</b>
	For use with 20A Twist-Lock® receptacles; receptacle not included. <i>Note: When mating with HBL26W09, 20A Non-NEMA plug, use HBL6800 cover.</i>	Yellow Black	<b>HBL6700</b> <b>HBL6700BK</b>
	For use with 30A Twist-Lock® receptacles; receptacle not included.	Yellow Black	<b>HBL6800</b> <b>HBL6800BK</b>



HBL28W75IN



HBL29W75IN

### Interiors

Device	125V		3Ø 250V AC		3Ø 480V AC	
	Plug	Receptacle	Plug	Receptacle	Plug	Receptacle
15A Straight Blade Locking	<b>HBL14W47IN</b> <b>HBL24W47IN</b>	<b>HBL15W47IN</b> —	— —	— —	— —	— —
20A Locking	—	<b>HBL27W47IN</b>	<b>HBL26W75IN</b>	—	<b>HBL26W76IN</b>	<b>HBL27W76IN</b>
30A Locking	—	—	<b>HBL28W75IN</b>	<b>HBL29W75IN</b>	<b>HBL28W76IN</b>	<b>HBL29W76IN</b>



HBLWTB1



HBL50W50

### Bushings, Cone Seals and Closure Caps

Device	Bushings	Cone Seals	Closure Caps	
			Yellow	Black
15A Straight Blade Locking	<b>HBLWTB1</b> <b>HBLWTB1</b>	<b>HBLWTCS1</b> <b>HBLWTCS1</b>	<b>HBL50W50</b> <b>HBL50W50</b>	<b>HBL50W50BK</b> <b>HBL50W50BK</b>
20A Straight Blade Locking	<b>HBLWTB1</b> <b>HBLWTB2</b>	<b>HBLWTCS1</b> <b>HBLWTCS2</b>	<b>HBL50W50</b> <b>HBL50W52</b>	<b>HBL50W50BK</b> <b>HBL50W52BK</b>
30A Locking	<b>HBLWTB3</b>	<b>HBLWTCS3</b>	<b>HBL50W54</b>	<b>HBL50W54BK</b>