




**HBL1221ILC**




**HBL1221PL**



**HBL1209**



**HBL1381**



**HBL1386I**

Dimensions in Inches (mm)

## HBL® Extra Heavy Duty Industrial Series, Illuminated Toggle Switches, Light ON with Load OFF

Description	Toggle Color	Rating	Single Pole	Double Pole	Three Way
Nylon toggle, back and side wired.	Ivory	15A 120/277V AC	<b>HBL1201IL</b>	—	<b>HBL1203IL</b>
	Ivory	20A 120/277V AC	<b>HBL1221IL</b>	—	<b>HBL1223IL</b>
	Clear		<b>HBL1221ILC</b>	—	<b>HBL1223ILC</b>
	Red		<b>HBL1221ILR</b>	—	—

## HBL® Extra Heavy Duty Industrial Series, Pilot Light Switches, Light ON with Load ON

Description	Toggle Color	Rating	Single Pole	Double Pole	Three Way
Nylon toggle, back and side wired.	Red	15A 120/277V AC	<b>HBL1201PL</b>	—	<b>HBL1203PL</b>
	Red	20A 120/277V AC	<b>HBL1221PL</b>	<b>HBL1222PL</b>	<b>HBL1223PL</b>
	Clear		<b>HBL1221PLC</b>	—	<b>HBL1223PLC</b>
	Green		<b>HBL1221PLG</b>	—	—
	Red	30A 120/277V AC	<b>HBL3031PL</b>	<b>HBL3032PL</b>	—

## HBL® Extra Heavy Duty Industrial Series, Momentary Contact, Specification Grade, Three Position, Two Circuit, Center OFF

Description	Toggle Color	15A, 120/277V AC	20A, 120/277V AC
Nylon toggle, back and side wired.	Brown	<b>HBL1556</b>	<b>HBL1557</b>
	Gray	<b>HBL1556GY</b>	<b>HBL1557GY</b>
	Ivory	<b>HBL1556I</b>	<b>HBL1557I</b>
	Light Almond	<b>HBL1556LA</b>	<b>HBL1557LA</b>
	Red	<b>HBL1556R</b>	—
	White	<b>HBL1556W</b>	<b>HBL1557W</b>
Key guide, back and side wired.	Black	<b>HBL1556L</b>	<b>HBL1557L</b>
	Gray	<b>HBL1556LG</b>	<b>HBL1557LG</b>
	Ivory	<b>HBL1556LI</b>	<b>HBL1557LI</b>
	White	<b>HBL1556LW</b>	<b>HBL1557LW</b>
Key for Locking switch.		<b>HBL1209</b>	

## HBL® Extra Heavy Duty Industrial Series, Maintained Contact, Specification Grade, Three Position, Two Circuit, Center OFF, Single Pole, Double Throw

Description	Toggle Color	15A 120/277V AC	20A 120/277V AC	30A 120/277V AC
Nylon toggle, back and side wired.	Brown	<b>HBL1381</b>	<b>HBL1385</b>	—
	Ivory	<b>HBL1381I</b>	<b>HBL1385I</b>	—
	White	—	<b>HBL1385W</b>	—

## Three Position, Two Circuit, Center OFF, Double Pole, Double Throw

Description	Toggle Color	15A 120/277V AC	20A 120/277V AC	30A 120/277V AC
Nylon toggle, back and side wired.	Brown	<b>HBL1382</b>	<b>HBL1386</b>	<b>HBL1388</b>
	Ivory	<b>HBL1382I</b>	<b>HBL1386I</b>	<b>HBL1388I</b>
Locking.		—	<b>HBL1386L</b>	—
Key for Locking switch.		—	<b>HBL1209</b>	—

Note: Keys are supplied with each locking switch. For extra keys order HBL1209. See page D-15 for accessories and page D-16 for wallplates. See page D-22 for technical information.

### HP Conversion Chart

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP
30A	2HP	2HP	2HP	2HP