



**IP67**  
SUITABILITY

## Housing Design

- Thermoplastic Cover on Plated Steel Base
- NEMA 1 Enclosure
- Pre-wired with LINKOSITY® Components
- Crush and Impact Resistance of MC Cable



## Housing Design

- High Impact PBT Enclosure
- Type 4X Enclosure
- Permanent Labelless Marking
- Lockable Handle to Meet OSHA Lockout/Tagout Regulations
- Cable Ratings: TC-ER, MTW, STOOW



## MotorQuick® Disconnect Switches

Type 1 Non-Metallic Enclosure 30A 3 Pole 600V AC	Catalog Number
HBL1389D with one pre-wired LINKOSITY® female receptacle (load side).	<b>HBL1389MQR</b>
HBL1389D with 5 foot pre-wired LINKOSITY® female cable (load side).	<b>HBL1389MQ5</b>
HBL1389D with one pre-wired LINKOSITY® male receptacle (line side) and one pre-wired LINKOSITY® female receptacle (load side).	<b>HBL1389MQR2</b>
Type 4X Non-Metallic Labelless Enclosure 30A 3 Pole 600V AC	Catalog Number
HBLDS3 with one pre-wired LINKOSITY® female receptacle (load side).	<b>HBLDS3MQR</b>
HBLDS3 with 5 foot pre-wired LINKOSITY® female cable (load side).	<b>HBLDS3MQ5</b>
HBLDS3 with one pre-wired LINKOSITY® male receptacle (line side) and one pre-wired LINKOSITY® female receptacle (load side).	<b>HBLDS3MQR2</b>
Type 4X Stainless Steel Enclosure 30A 3 Pole 600V AC	Catalog Number
HBLDS3SS with one pre-wired LINKOSITY® female receptacle (load side).	<b>HBLDS3SSRMQR</b> <b>HBLDS3SSMQR</b>
HBLDS3SS with 5 foot pre-wired LINKOSITY® female cable (load side).	<b>HBLDS3SSRMQ5</b> <b>HBLDS3SSMQ5</b>
HBLDS3SS with one pre-wired LINKOSITY® male receptacle (line side) and one pre-wired LINKOSITY® female receptacle (load side).	<b>HBLDS3SSRMQR2</b> <b>HBLDS3SSMQR2</b>




## Accessories

Description	Catalog Number
3P 4W LINKOSITY® male receptacle for installation on motor.	<b>RM3004PA001</b>
3P 4W LINKOSITY® female receptacle for installation in switch.	<b>RF3004PA001</b>
3P 4W LINKOSITY® double ended (male/female) 5-50 foot cable.	<b>PH3004PAxxx*</b>
3P 4W LINKOSITY® single ended (female) 5-50 foot cable.	<b>PF3004PAxxx*</b>
Cord connector, ¼ in. NPT .63-.75 in. (16.0-19.1) diameter.	<b>SHC1037CR</b>
Lock-on cover for LINKOSITY® connections.	<b>PH2030C</b>

Note: \*Cables available from 5-50 feet in 5 foot increments. To purchase larger cable, replace the **xxx** with the required length in feet. (Examples: **PH3004PA005** = 5 foot cable, **PH3004PA050** = 50 foot cable.)

## Sample Set Up

(1) **HBLDS3MQR** + (1) **PH3004PAxxx** + (1) **RM3004PA001** = **Total Set Up\*\***



Note: \*\* Retrofit parts available for pre-existing disconnect switch installations. Please consult factory for availability.