

Switched Disconnects and Enclosures

Ratings Quick Reference Guide

Circuit-Lock® Switched Enclosures

Amp Description	Phase	Poles	HP				Catalog Number
			120	240	480	600	
30 TYPE 1 Non-Metallic	3	3	3	7.5	15	20	HBL1389MQR
TYPE 1 Non-Metallic	3	3	3	7.5	15	20	HBL1389MQ5
TYPE 1 Non-Metallic	3	3	3	7.5	15	20	HBL1389MQR2
NEMA 1 Aluminum	1	2	2	5	10	15	HBL1372
NEMA 1 Aluminum	3	3	3	7.5	15	20	HBL1379
NEMA 1 Non-Metallic	1	2	2	5	10	15	HBL1392
NEMA 1 Non-Metallic	3	3	3	7.5	15	20	HBL1389
NEMA 3/3R Non-Metallic	1	2	2	5	10	15	HBL13R22
NEMA 3/3R Non-Metallic	3	3	3	7.5	15	20	HBL13R23
NEMA 3R Die Cast Aluminum	1	2	2	5	10	15	HBL13R12
NEMA 3R Die Cast Aluminum	3	3	3	7.5	15	20	HBL13R13
NEMA 3R Aluminum	1	2	2	5	10	15	HBL13R92
NEMA 3R Aluminum	3	3	3	7.5	15	20	HBL13R89
IP69k TYPE 4X Labelless Non-Metallic	3	3	1	7.5	15	15	HBLDS3
IP69k TYPE 4X Labelless Non-Metallic	3	3	1	7.5	15	15	HBLDS3AC
IP69k TYPE 4X Labelless Non-Metallic	3	3	1	7.5	15	15	HBLDS3NK
IP69k TYPE 4X Labelless Non-Metallic	3	3	1	7.5	15	15	HBLDS3ACNK
IP69k TYPE 4X Labelless Non-Metallic	3	3	1	5	10	10	HBLDS33ACNK
TYPE 4X Labelless Non-Metallic	3	3	1	7.5	15	15	HBLDS3MQR
TYPE 4X Labelless Non-Metallic	3	3	1	7.5	15	15	HBLDS3MQ5
TYPE 4X Labelless Non-Metallic	3	3	1	7.5	15	15	HBLDS3MQR2
IP69k TYPE 4X Stainless Steel	3	3	1	7.5	15	15	HBLDS3SS
IP69k TYPE 4X Stainless Steel	3	3	1	7.5	15	15	HBLDS3SSAC
IP69k TYPE 4X Stainless Steel	3	3	1	7.5	15	15	HBLDS3SSVFD
TYPE 4X Stainless Steel	3	3	1	7.5	15	15	HBLDS3SSMQR
TYPE 4X Stainless Steel	3	3	1	7.5	15	15	HBLDS3SSMQ5
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	1	7.5	15	15	HBLDS3SSR
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	1	7.5	15	15	HBLDS3SSR2K
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	1	7.5	15	15	HBLDS3SSRVFD
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	1	7.5	15	15	HBLDS3SSRAC
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	1	7.5	15	15	HBLDS3SSRMQR
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	1	7.5	15	15	HBLDS3SSRMQ5
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	1	7.5	15	15	HBLDS3SSRMQR2
TYPE 4X Non-Metallic Fused Disconnect	3	3	1	7.5	15	20	FDS30
NEMA 4X Stainless Steel	3	3	3	7.5	15	20	HBL13S33D
NEMA 4X Non-Metallic	3	3	3	7.5	15	20	HBL13X33D
60 NEMA 3R Aluminum	1	2	—	10	15	20	HBL16R92D
NEMA 3R Aluminum	3	3	—	10	25	30	HBL16R93D
IP69k TYPE 4X Non-Metallic	3	3	7.5	30	50	50	HBLDS6
IP69k TYPE 4X Non-Metallic	3	3	7.5	30	50	50	HBLDS6AC
IP69k TYPE 4X Stainless Steel	3	3	7.5	30	50	50	HBLDS6SS
IP69k TYPE 4X Stainless Steel	3	3	7.5	30	50	50	HBLDS6SSAC
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	7.5	30	50	50	HBLDS6SSR
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	7.5	30	50	50	HBLDS6SSRVFD
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	7.5	30	50	50	HBLDS6SSRAC
TYPE 4X Non-Metallic Fused Disconnect	3	3	3	15	30	40	FDS60
NEMA 4X Stainless Steel	3	3	—	10	25	30	HBL16S63D
NEMA 4X Non-Metallic	3	3	—	10	25	30	HBL16X63D
100 IP69k TYPE 4X Non-Metallic	3	3	7.5	30	50	50	HBLDS10
IP69k TYPE 4X Non-Metallic	3	3	7.5	30	50	50	HBLDS10AC
IP69k TYPE 4X Stainless Steel	3	3	7.5	30	50	50	HBLDS10SS
IP69k TYPE 4X Stainless Steel	3	3	7.5	30	50	50	HBLDS10SSAC
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	7.5	30	50	50	HBLDS10SSR
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	7.5	30	50	50	HBLDS10SSRVFD
IP69k TYPE 4X, 12 and IP69k Sloped, SS	3	3	7.5	30	50	50	HBLDS10SSRAC
200 Type 4X, 12 Non-Metallic			10	75	150	200	HBLDS20
Type 4X, 12 Stainless Steel			10	75	150	200	HBLDS20SS

Note: HP ratings apply to Jog and LED versions.



HBL1379



HBL1389MQR



HBL1379



HBL16R93D



HBLDS3



FDS30



HBLDS3P



HBLDS3J



HBLDS3MQR



HBLDS3MQ5



HBLDS3SS



HBLDS3SSR



HBLDS20



HBLDS20SS