

Pin and Sleeve Devices/Mechanical Interlocks

Watertight Series North American Ratings



Amps	Dual Rated:	Ratings	Watertight IP67 Suitability			
			Inlet*	Connector	Plug	Receptacle
16 & 20		2P/3W, 20A 125V AC	C320B4WA	C320C4WA	C320P4WA	C320R4WA
	Dual Rated:	2P/3W, 20A 250V AC/16A 220-240V	C320B6WA	C320C6WA	C320P6WA	C320R6WA
		2P/3W, 20A 480V AC	C320B7WA	C320C7WA	C320P7WA	C320R7WA
		3P/4W, 20A 3P 600V	C420B5WA	C420C5WA	C420P5WA	C420R5WA
	Dual Rated:	2P/3W, 20A 250V AC/16A 220-240V	C420B6WA	C420C6WA	C420P6WA	C420R6WA
		3P/4W, 20A 3P 480V	C420B7WA	C420C7WA	C420P7WA	C420R7WA
	Dual Rated:	3P/4W, 16/20A 3P 250 VAC	C420B9WA	C420C9WA	C420P9WA	C420R9WA
		4P/5W, 20A 347/600V	C520B5WA	C520C5WA	C520P5WA	C520R5WA
	Dual Rated:	4P/5W, 16/20A 200-415V AC	C520B6WA	C520C6WA	C520P6WA	C520R6WA
		4P/5W, 20A 277/480V	C520B7WA	C520C7WA	C520P7WA	C520R7WA
Dual Rated:	4P/5W, 16/20A 120/208V	C520B9WA	C520C9WA	C520P9WA	C520R9WA	
30 & 32		2P/3W, 30A 125V AC	C330B4WA	C330C4WA	C330P4WA	C330R4WA
	Dual Rated:	2P/3W, 30A 250V/32A 220-240V	C330B6WA	C330C6WA	C330P6WA	C330R6WA
		2P/3W, 30A 480V AC	C330B7WA	C330C7WA	C330P7WA	C330R7WA
		3P/4W, 30A 3P 600V	C430B5WA	C430C5WA	C430P5WA	C430R5WA
	Dual Rated:	3P/4W, 30/32A 380-415V AC	C430B6WA	C430C6WA	C430P6WA	C430R6WA
		3P/4W, 30A 3P 480V	C430B7WA	C430C7WA	C430P7WA	C430R7WA
	Dual Rated:	3P/4W, 30/32A 3P 250 VAC	C430B9WA	C430C9WA	C430P9WA	C430R9WA
		4P/5W, 30A 347/600V	C530B5WA	C530C5WA	C530P5WA	C530R5WA
	Dual Rated:	4P/5W, 30/32A 200-415V AC	C530B6WA	C530C6WA	C530P6WA	C530R6WA
		4P/5W, 30A 277/480V	C530B7WA	C530C7WA	C530P7WA	C530R7WA
Dual Rated:	4P/5W, 30/32A 120/208V	C530B9WA	C530C9WA	C530P9WA	C530R9WA	
60 & 63		2P/3W, 60A 125V AC	C360B4WA	C360C4WA	C360P4WA	C360R4WA
	Dual Rated:	2P/3W, 60A 250V/63A 220-240V	C360B6WA	C360C6WA	C360P6WA	C360R6WA
		2P/3W, 60A 480V AC	C360B7WA	C360C7WA	C360P7WA	C360R7WA
		3P/4W, 60A 3P 600V	C460B5WA	C460C5WA	C460P5WA	C460R5WA
	Dual Rated:	3P/4W, 60/63A 380-415V AC	C460B6WA	C460C6WA	C460P6WA	C460R6WA
		3P/4W, 60A 3P 480V	C460B7WA	C460C7WA	C460P7WA	C460R7WA
	Dual Rated:	3P/4W, 60/63A 3P 250 VAC	C460B9WA	C460C9WA	C460P9WA	C460R9WA
		4P/5W, 60A 347/600V	C560B5WA	C560C5WA	C560P5WA	C560R5WA
	Dual Rated:	4P/5W, 60/63A 200-415V AC	C560B6WA	C560C6WA	C560P6WA	C560R6WA
		4P/5W, 60A 277/480V	C560B7WA	C560C7WA	C560P7WA	C560R7WA
Dual Rated:	4P/5W, 60/63A 120/208V	C560B9WA	C560C9WA	C560P9WA	C560R9WA	

See page G-28 for Back Boxes and G-36 for product dimensions.

* Adapter plates required for mounting to Hubbell back boxes. 20 & 30A use AP2030, 60A use AP60 and 100A use AP100.