

Pin and Sleeve Devices/Mechanical Interlocks

Watertight Series North American Ratings (Cont'd)



| Amps | Dual Rated: | Ratings | Watertight IP67 Suitability | | | |
|-----------|-------------|-----------------------------------|-----------------------------|-----------|-----------|-------------|
| | | | Inlet* | Connector | Plug | Receptacle* |
| 100 & 125 | Dual Rated: | 2P/3W, 100A 250V AC/125A 220-240V | C3100B6WA | C3100C6WA | C3100P6WA | C3100R6WA |
| | | 2P/3W, 100A 480V AC | C3100B7WA | C3100C7WA | C3100P7WA | C3100R7WA |
| | | 3P/4W, 100A 3P 600V | C4100B5WA | C4100C5WA | C4100P5WA | C4100R5WA |
| | Dual Rated: | 3P/4W, 100/125A 380-415V AC | C4100B6WA | C4100C6WA | C4100P6WA | C4100R6WA |
| | | 3P/4W, 100A 3P 480V | C4100B7WA | C4100C7WA | C4100P7WA | C4100R7WA |
| | Dual Rated: | 3P/4W, 100/125A 3P 250 VAC | C4100B9WA | C4100C9WA | C4100P9WA | C4100R9WA |
| | | 4P/5W, 100A 347/600V | C5100B5WA | C5100C5WA | C5100P5WA | C5100R5WA |
| | Dual Rated: | 4P/5W, 100/125A 200-415V AC | C5100B6WA | C5100C6WA | C5100P6WA | C5100R6WA |
| | | 4P/5W, 100A 277/480V | C5100B7WA | C5100C7WA | C5100P7WA | C5100R7WA |
| | Dual Rated: | 4P/5W, 100/125A 120/208V | C5100B9WA | C5100C9WA | C5100P9WA | C5100R9WA |

Watertight Series International Ratings



| Amps | Ratings | Watertight IP67 Suitability | | | |
|------|----------------------|-----------------------------|-----------|-----------|-------------|
| | | Inlet* | Connector | Plug | Receptacle* |
| 16A | 2P/3W, 16A 100-130V | C316B4WA | C316C4WA | C316P4WA | C316R4WA |
| | 2P/3W, 16A 220-240V | C316B6WA | C316C6WA | C316P6WA | C316R6WA |
| | 2P/3W, 16A 380-415V | C416B6WA | C416C6WA | C416P6WA | C416R6WA |
| | 4P/5W, 16A 200-415V | C516B6WA | C516C6WA | C516P6WA | C516R6WA |
| 32A | 2P/3W, 32A 100-130V | C332B4WA | C332C4WA | C332P4WA | C332R4WA |
| | 2P/3W, 32A 220-240V | C332B6WA | C332C6WA | C332P6WA | C332R6WA |
| | 3P/4W, 32A 380-480V | C432B3WA | C432C3WA | C432P3WA | C432R3WA |
| | 3P/4W, 32A 380-415V | C432B6WA | C432C6WA | C432P6WA | C432R6WA |
| | 4P/5W, 32A 200-415V | C532B6WA | C532C6WA | C532P6WA | C532R6WA |
| 63A | 2P/3W, 63A 220-240V | C363B6WA | C363C6WA | C363P6WA | C363R6WA |
| | 3P/4W, 63A 380-415V | C463B6WA | C463C6WA | C463P6WA | C463R6WA |
| | 4P/5W, 63A 200-415V | C563B6WA | C563C6WA | C563P6WA | C563R6WA |
| 125A | 2P/3W, 125A 220-240V | C3125B6WA | C3125C6WA | C3125P6WA | C3125R6WA |
| | 3P/4W, 125A 380-415V | C4125B6WA | C4125C6WA | C4125P6WA | C4125R6WA |
| | 4P/5W, 125A 200-415V | C5125B6WA | C5125C6WA | C5125P6WA | C5125R6WA |

See page G-28 for Back Boxes and G-36 for product dimensions.

* Adapter plates required for mounting to Hubbell back boxes. 20& 30A use AP2030, 60A use AP60 and 100A use AP100.