

# Pin and Sleeve Devices/Mechanical Interlocks

## Splashproof Series North American Ratings

Amps	Ratings	Splashproof IP44 Suitability			
		Inlet*	Connector	Plug	Receptacle*
16 & 20	2P/3W, 20A 125V AC	C320B4SA	C320C4SA	C320P4SA	C320R4SA
	Dual Rated 2P/3W, 20A 250V AC/16A 220-240V	C320B6SA	C320C6SA	C320P6SA	C320R6SA
	2P/3W, 20A 480V AC	C320B7SA	C320C7SA	C320P7SA	C320R7SA
	3P/4W, 20A 3Ø 600V	C420B5SA	C420C5SA	C420P5SA	C420R5SA
	Dual Rated 2P/3W, 20A 250V AC/16A 220-240V	C420B6SA	C420C6SA	C420P6SA	C420R6SA
	3P/4W, 20A 3Ø 480V	C420B7SA	C420C7SA	C420P7SA	C420R7SA
	Dual Rated 3P/4W, 16/20A 3P 250 VAC	C420B9SA	C420C9SA	C420P9SA	C420R9SA
	4P/5W, 20A 347/600V	C520B5SA	C520C5SA	C520P5SA	C520R5SA
	Dual Rated 4P/5W, 16/20A 200-415V AC	C520B6SA	C520C6SA	C520P6SA	C520R6SA
	4P/5W, 20A 277/480V	C520B7SA	C520C7SA	C520P7SA	C520R7SA
Dual Rated 4P/5W, 16/20A 120/208V	C520B9SA	C520C9SA	C520P9SA	C520R9SA	
30 & 32	2P/3W, 30A 125V AC	C330B4SA	C330C4SA	C330P4SA	C330R4SA
	Dual Rated 2P/3W, 30A 250V AC/32A 220-240V	C330B6SA	C330C6SA	C330P6SA	C330R6SA
	2P/3W, 30A 480V AC	C330B7SA	C330C7SA	C330P7SA	C330R7SA
	3P/4W, 30A 3Ø 600V	C430B5SA	C430C5SA	C430P5SA	C430R5SA
	Dual Rated 3P/4W, 30/32A 380-415V AC	C430B6SA	C430C6SA	C430P6SA	C430R6SA
	3P/4W, 30A 3Ø 480V	C430B7SA	C430C7SA	C430P7SA	C430R7SA
	Dual Rated 3P/4W, 30/32A 3P 250 VAC	C430B9SA	C430C9SA	C430P9SA	C430R9SA
	4P/5W, 30A 347/600V	C530B5SA	C530C5SA	C530P5SA	C530R5SA
	Dual Rated 4P/5W, 30/32A 200-415V AC	C530B6SA	C530C6SA	C530P6SA	C530R6SA
	4P/5W, 30A 277/480V	C530B7SA	C530C7SA	C530P7SA	C530R7SA
Dual Rated 4P/5W, 30/32A 120/208V	C530B9SA	C530C9SA	C530P9SA	C530R9SA	
60 & 63	2P/3W, 60A 125V AC	C360B4SA	C360C4SA	C360P4SA	C360R4SA
	Dual Rated 2P/3W, 60A 250V AC/63A 220-240V	C360B6SA	C360C6SA	C360P6SA	C360R6SA
	2P/3W, 60A 480V AC	C360B7SA	C360C7SA	C360P7SA	C360R7SA
	3P/4W, 60A 3Ø 600V	C460B5SA	C460C5SA	C460P5SA	C460R5SA
	Dual Rated 3P/4W, 60/63A 380-415V AC	C460B6SA	C460C6SA	C460P6SA	C460R6SA
	3P/4W, 60A 3Ø 480V	C460B7SA	C460C7SA	C460P7SA	C460R7SA
	Dual Rated 3P/4W, 60/63A 3P 250 VAC	C460B9SA	C460C9SA	C460P9SA	C460R9SA
	4P/5W, 60A 347/600V	C560B5SA	C560C5SA	C560P5SA	C560R5SA
	Dual Rated 4P/5W, 60/63A 200-415V AC	C560B6SA	C560C6SA	C560P6SA	C560R6SA
	4P/5W, 60A 277/480V	C560B7SA	C560C7SA	C560P7SA	C560R7SA
Dual Rated 4P/5W, 60/63A 120/208V	C560B9SA	C560C9SA	C560P9SA	C560R9SA	

See page G-28 for Back Boxes. Dimensions are available online.

\* Adapter plates required for mounting to Hubbell back boxes. 20 & 30A use AP2030, 60A use AP60 and 100A use AP100.