

Pin and Sleeve Devices/Mechanical Interlocks



Splashproof Series International Ratings

Amps	Ratings	Splashproof IP44 Suitability			
		Inlet	Connector	Plug	Receptacle
16A	2P/3W, 16A 100-130V	C316B4SA	C316C4SA	C316P4SA	C316R4SA
	2P/3W, 16A 220-240V	C316B6SA	C316C6SA	C316P6SA	C316R6SA
	2P/3W, 16A 380-415V	C416B6SA	C416C6SA	C416P6SA	C416R6SA
	4P/5W, 16A 200-415V	C516B6SA	C516C6SA	C516P6SA	C516R6SA
32A	2P/3W, 32A 100-130V	C332B4SA	C332C4SA	C332P4SA	C332R4SA
	2P/3W, 32A 220-240V	C332B6SA	C332C6SA	C332P6SA	C332R6SA
	3P/4W, 32A 380-480V	C432B3SA	C432C3SA	C432P3SA	C432R3SA
	3P/4W, 32A 380-415V	C432B6SA	C432C6SA	C432P6SA	C432R6SA
	4P/5W, 32A 200-415V	C532B6SA	C532C6SA	C532P6SA	C532R6SA
63A	2P/3W, 63A 220-240V	C363B6SA	C363C6SA	C363P6SA	C363R6SA
	3P/4W, 63A 380-415V	C463B6SA	C463C6SA	C463P6SA	C463R6SA
	4P/5W, 63A 200-415V	C563B6SA	C563C6SA	C563P6SA	C563R6SA

Liquid Tight Versions

Amps	Ratings	Liquid Tight Conduit Size	IP67 Connectors	IP44 Connectors	IP67 Plugs*	IP44 Plugs*
30A	5h 3ØY 347/600 V	1/2"	C530C5WLT12	C530C5SLT12	C530P5WA	C530P5SA
30A	5h 3ØY 347/600 V	3/4"	C530C5WLT34	C530C5SLT34	C530P5WA	C530P5SA
30A / 32A	6h 3Ø 200/346-240/415 AC	1/2"	C530C6WLT12	C530C6SLT12	C530P6WA	C530P6SA
30A / 32A	6h 3Ø 200/346-240/415 AC	3/4"	C530C6WLT34	C530C6SLT34	C530P6WA	C530P6SA
30A	7h 3ØY 277/480 V	1/2"	C530C7WLT12	C530C7SLT12	C530P7WA	C530P7SA
30A	7h 3ØY 277/480 V	3/4"	C530C7WLT34	C530C7SLT34	C530P7WA	C530P7SA
30A / 32A	9h 3ØY 120/208 V	1/2"	C530C9WLT12	C530C9SLT12	C530P9WA	C530P9SA
30A / 32A	9h 3ØY 120/208 V	3/4"	C530C9WLT34	C530C9SLT34	C530P9WA	C530P9SA
60A	4h 125 VAC	3/4"	C360C4WLT34	C360C4SLT34	C360P4WA	C360P4SA
60A / 63A	6h 250 VAC	3/4"	C360C6WLT34	C360C6SLT34	C360P6WA	C360P6SA
60A	7h 480 VAC	3/4"	C360C7WLT34	C360C7SLT34	C360P7WA	C360P7SA
60A	5h 3ØY 347/600 V	3/4"	C460C5WLT34	C460C5SLT34	C460P5WA	C460P5SA
60A / 63A	6h 3Ø 200/346-240/415 AC	3/4"	C460C6WLT34	C460C6SLT34	C460P6WA	C460P6SA
60A	7h 3Ø 480 V	3/4"	C460C7WLT34	C460C7SLT34	C460P7WA	C460P7SA
60A / 63A	9h 3ØY 120/208 V	3/4"	C460C9WLT34	C460C9SLT34	C460P9WA	C460P9SA
60A	5h 3ØY 347/600 V	3/4"	C560C5WLT34	C560C5SLT34	C560P5WA	C560P5SA
60A / 63A	6h 3Ø 200/346-240/415 AC	3/4"	C560C6WLT34	C560C6SLT34	C560P6WA	C560P6SA
60A	7h 3ØY 277/480 V	3/4"	C560C7WLT34	C560C7SLT34	C560P7WA	C560P7SA
60A / 63A	9h 3ØY 120/208 V	3/4"	C560C9WLT34	C560C9SLT34	C560P9WA	C560P9SA

Dimensions available online

* Mating plugs are certified for installation on cable only.