

PANEL-SAFE® Power Only

Description	NEMA TYPE 4	NEMA TYPE 4X
15A 125V GFCI with In-Cabinet Receptacle.	PR20	—



PR20

PANEL-SAFE® Data Only

Description	NEMA TYPE 4	NEMA TYPE 4X
Cat. 5e Ethernet Access only.	P5E	P4X5E
DB9 Interface Connector only.	PDB9	—
PANEL-SAFE Data Port with DB9 Connector.	PDB9MF	—
DH + Combo (DB9/8M Din) and Cat. 5e Ethernet.	PDH5E	—
PANEL-SAFE Data Port, (2) USB, 3 ft. Cable.	—	P4XUSBA2C3



P5E



PDB9MF



P4XUSBA2C3

PANEL-SAFE® Power and Data

Description	NEMA TYPE 4	NEMA TYPE 4X
15A 125V GFCI with In-Cabinet Receptacle and Cat. 5e Ethernet Access.	PR205E	PR4X205E
15A 125V GFCI with In-Cabinet Receptacle, Cat. 5e Ethernet Access and 3A Circuit Breaker.	PR205EB	PR4X205EB
PANEL-SAFE with 15A GFCI and Cat.5e, DB9 and 3A Circuit Breaker.	PR205EDB9B	—
PANEL-SAFE with 15A GFCI and Cat.5e, 3A USB.	PR205EUSBA	—
PANEL-SAFE with 15A GFCI and Cat.5e, (2) 3A USB.	PR205EUSBA2	—
PANEL-SAFE Data Access Port.	PR205EUSBA2VGA	—
15A 125V GFCI Power and Cat. 5e, DB9 and 3A Circuit Breaker.	PR205EDB9MFB	—
15A 125V GFCI Power and Cat. 5e Ethernet, DH + Combo (DB9/8M Din).	P20DH5E	—
PANEL-SAFE with 15A GFCI and Cat.5/DB9.	P205EDB9	—
PANEL-SAFE, 4X, Cat. 5e, DB9, Circuit Breaker.	—	PR4X205EDB9B
PANEL-SAFE 4X, Cat. 5e, (2) DB9, Circuit Breaker.	—	PR4X205E2DB92B
15A 125V Power and Cat. 5e Ethernet Access.	P155E	P4X155E
15A 125V Power, Cat. 5e Ethernet Access and 3A Circuit Breaker.	P155EB	P4X155EB
15A 125V Power and (2) Cat. 5e Ethernet Access.	P155E2	—
15A 120V AC Power, NEMA 12/4, DB9 M/F, 10 ft. Cable.	P15DB9MFC10	—
15A 125V Power and DH485 Interface (RJ-45F to RJ-45M, 10 ft. Cable).	P15DH485C10	—
15A 125V Power and Micrologix 8M Din/F to 8M Din/M, 10 ft. Cable.	P15ML8F8MC10	—



PR205EUSBA2



PR205EB



P155E



P155EB

Additional computer interfaces, PLC connections and configurations available upon request. Consult factory for catalog number and availability.