

LINKOSITY® UL Type 3R and 4X Rated Assemblies

- Available with switch, ground fault, corrosion resistant or isolated ground receptacle types
- LINKOSITY® power pass through option
- Fed with LINKOSITY® power cable and receptacle
- UL Type 3R and 4X Rated
- Device identification marking
- Versatile mounting provision



LINKOSITY® Feed - UL Type 3R Rated*

3R Rated Standard Items

Description	Catalog Number
20A 125V Ground Fault	M3R002SGGF0
20A 125V Switched, Spec Grade	M3RSL1SG000
20A 125V Switched, Ground Fault	M3RSL1SGGF0
20A 125V Spec Grade	M3R002SG000
20A 125V Ground Fault, Pass-Thru	M3R002SGGFP
20A 125V Switched, Spec Grade, Pass-Thru	M3RSL1SG00P
20A 125V Switched, Ground Fault, Pass-Thru	M3RSL1SGGFP
20A 125V (2) Switches	M3R2SG000
20A 125V 1-Gang Ground Fault	M3R001SGGF0
20A 125V Corrosion Resistant	M3R002CR000
20A 125V Isolated Ground	M3R002SGIGP
20A 125V Spec Grade, Pass-Thru	M3R002SG00P

Note: *When cover closed.



Device Type	Style	Type	No. of Devices	Device Type	Device Feature	Pass-Thru
M	3R - 3R Lids	SL - Switch Local	1	SG - Spec Grade	IG - Isolated Ground	P - Pass-Thru
	3D - 3R Deep Cover	SM - Switch Master	2	HG - Hospital Grade	GF - Ground Fault	0 - No Pass-Thru
		00 - None		CR - Corrosion Resistant	SI - Surge/IG	
				L1 - 15A Locking	SS - Surge	
					00 - Standard	

Replacement Mounting Feet

Description	Catalog Number
For Power Distribution Assemblies.	HBLRFT1^Δ

Note: ^Δ Package of 10 mounting feet and 10 screws.

