

MotorQuick® Disconnect Switches

Housing Design

- Thermoplastic Cover on Plated Steel Base
- NEMA 1 Enclosure
- Pre-wired with LINKOSITY® Components
- Crush and Impact Resistance of MC Cable



HBL1389MQ5

IP67
SUITABILITY

Housing Design

- High Impact Valox® Enclosure
- Type 4X Enclosure
- Permanent Labelless Marking
- Lockable Handle to Meet OSHA Lockout/Tagout Regulations
- Cable Ratings:
TC-ER, MTW, STOOW



HBLDS3MQ5

MotorQuick® Disconnect Switches

Type 1 Non-Metallic Enclosure 30A 3 Pole 600V AC

HBL1389D with one pre-wired LINKOSITY® female receptacle (load side).

HBL1389D with 5 foot pre-wired LINKOSITY® female cable (load side).

HBL1389D with one pre-wired LINKOSITY® male receptacle (line side) and one pre-wired LINKOSITY® female receptacle (load side).

Catalog Number

HBL1389MQR

HBL1389MQ5

HBL1389MQR2

Type 4X Non-Metallic Labelless Enclosure 30A 3 Pole 600V AC

HBLDS3 with one pre-wired LINKOSITY® female receptacle (load side).

HBLDS3 with 5 foot pre-wired LINKOSITY® female cable (load side).

HBLDS3 with one pre-wired LINKOSITY® male receptacle (line side) and one pre-wired LINKOSITY® female receptacle (load side).

HBLDS3MQR

HBLDS3MQ5

HBLDS3MQR2

Type 4X Stainless Steel Enclosure 30A 3 Pole 600V AC

HBLDS3SS with one pre-wired LINKOSITY® female receptacle (load side).

HBLDS3SS with 5 foot pre-wired LINKOSITY® female cable (load side).

HBLDS3SS with one pre-wired LINKOSITY® male receptacle (line side) and one pre-wired LINKOSITY® female receptacle (load side).

Sloped Top

Square Top

HBLDS3SSRMQR **HBLDS3SSMQR**

HBLDS3SSRMQ5 **HBLDS3SSMQ5**

HBLDS3SSRMQR2 **HBLDS3SSMQR2**



HBL1389MQR2



HBLDS3MQR



HBLDS3SSRMQR



HBLDS3SSMQR

Accessories

Description

3P 4W LINKOSITY® male receptacle for installation on motor.

3P 4W LINKOSITY® female receptacle for installation in switch.

3P 4W LINKOSITY® double ended (male/female) 5-50 foot cable.

3P 4W LINKOSITY® single ended (female) 5-50 foot cable.

Cord connector, 3/4 in. NPT .63-.75 in. (16.0-19.1) diameter.

Lock-on cover for LINKOSITY® connections.

Catalog Number

RM3004PA001

RF3004PA001

PH3004PAxxx*

PF3004PAxxx*

SHC1037CR

PH2030C

Note: *Cables available from 5-50 feet in 5 foot increments. To purchase larger cable, replace the **xxx** with the required length in feet. (Examples: **PH3004PA005** = 5 foot cable, **PH3004PA050** = 50 foot cable.)

Sample Set Up

(1) HBLDS3MQR + (1) PH3004PAxxx + (1) RM3004PA001 =

Total Set Up**



+



+



=



Note: ** Retrofit parts available for pre-existing disconnect switch installations. Please consult factory for availability.

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.



PH2030C